

2SD1277, 2SD1277A

Silicon NPN triple diffusion planar type Darlington

For midium speed power switching


Complementary to 2SB951 and 2SB951A

■ Features


- High foward current transfer ratio h_{FE}
- High-speed switching
- Full-pack package which can be installed to the heat sink with one screw

■ Absolute Maximum Ratings ($T_C=25^{\circ}\text{C}$)

Parameter		Symbol	Ratings	Unit
Collector to base voltage	2SD1277	V_{CBO}	60	V
	2SD1277A		80	
Collector to emitter voltage	2SD1277	V_{CEO}	60	V
	2SD1277A		80	
Emitter to base voltage		V_{EBO}	7	V
Peak collector current		I_{CP}	12	A
Collector current		I_C	8	A
Collector power dissipation	$T_C=25^{\circ}\text{C}$	P_C	45	W
	$T_a=25^{\circ}\text{C}$		2	
Junction temperature		T_j	150	$^{\circ}\text{C}$
Storage temperature		T_{stg}	-55 to +150	$^{\circ}\text{C}$



Internal Connection









■ Electrical Characteristics ($T_C=25^{\circ}\text{C}$)


Parameter		Symbol	Conditions	min	typ	max	Unit
Collector cutoff current	2SD1277	I _{CBO}	V _{CB} = 60V, I _E = 0			100	μA
	2SD1277A		V _{CB} = 80V, I _E = 0			100	
Emitter cutoff current		I _{EBO}	V _{EB} = 7V, I _C = 0			2	mA
Collector to emitter voltage	2SD1277	V _{CEO}	I _C = 30mA, I _B = 0	60			V
	2SD1277A			80			
Forward current transfer ratio		h _{FE1} *	V _{CE} = 3V, I _C = 4A	2000		10000	
		h _{FE2}	V _{CE} = 3V, I _C = 8A	500			
Collector to emitter saturation voltage		V _{CE(sat)}	I _C = 4A, I _B = 8mA			1.5	V
Base to emitter saturation voltage		V _{BE(sat)}	I _C = 4A, I _B = 8mA			2	V
Transition frequency		f _T	V _{CE} = 10V, I _C = 0.5A, f = 1MHz	20			MHz
Turn-on time		t _{on}	I _C = 4A, I _{B1} = 8mA, I _{B2} = -8mA, V _{CC} = 50V		0.5		μs
Storage time		t _{stg}			4		μs
Fall time		t _f			1		μs

* h_{FE1} Rank classification

Rank	Q	P
h_{FE1}	2000 to 5000	4000 to 10000

$P_C - T_a$  $I_C - V_{CE}$  $V_{CE(sat)} - I_C$  $V_{CE(sat)} - I_C$  $V_{CB(sat)} - I_C$  $h_{FE} - I_C$ 

Area of safe operation (ASO)

 $R_{th(t)} - t$ 