




PC board drilling dimensions(after plating)
(thickness ≤ 3.20±0.30mm)



TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P90C4PA00	D09P90C6PA00
15	39.14	33.32	25.18	25.12	19.18	D15P90C4PA00	D15P90C6PA00
25	53.03	47.04	39.12	38.84	33.12	D25P90C4PA00	D25P90C6PA00
37	69.32	63.50	55.68	55.30	49.68	D37P90C4PA00	D37P90C6PA00

gold flash 0.76» gold

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P90C4PA00LF	D09P90C6PA00LF
15	39.14	33.32	25.18	25.12	19.18	D15P90C4PA00LF	D15P90C6PA00LF
25	53.03	47.04	39.12	38.84	33.12	D25P90C4PA00LF	D25P90C6PA00LF
37	69.32	63.50	55.68	55.30	49.68	D37P90C4PA00LF	D37P90C6PA00LF

gold flash 0.76» gold

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

European Views

www.fciconnect.com				surface	ISO 1302	tolerance std	ISO 406	ISO 1101	projection	mm	Scale
				ISO 1302	tolerance std	ISO 406	ISO 1101	projection	mm	Scale	
				tolerances unless otherwise specified	tolerances unless otherwise specified	tolerances unless otherwise specified	tolerances unless otherwise specified	tolerances unless otherwise specified	tolerances unless otherwise specified	tolerances unless otherwise specified	tolerances unless otherwise specified
Dr	PESSON	1991-09-18	ANGULAR	0.X	±0.1	size	A3	2	Rev.		
Eng	PESSON	1991-09-18	LINEAR	0.XX	±0.1	size	A3	2	Rev.		
Chr	NIRMAL GEORGE	2009-11-24	0.XX	±0.1	ECN	109-0268					
Appr	SUDHIR VARMA	2009-11-24	Product family	D-SUB	Spec ref	-					
MALE CONNECTOR DELTA D LOW PROFIL				straight press-fit							
C01-8646-0091				CUSTOMER	sheet	1 of 1					

