




HONEYWELL PART NUMBER
141SM32-H2
PRODUCT CODE TYS0299

REV	DOCUMENT	CHANGED BY	CHECK
3	0041782	PK 21JUL08	ASD



NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF Ø.087 MAX ON .375±.002 CENTERS
- 2 - TERMINALS ARE PLATED FOR SOLDERING
- 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 250°F
- 4 - CHARACTERISTICS TAKEN AT POINT "A"
- 5 - CUSTOMER'S TARGET DIFF TRAVEL RANGE AT POINT A ON LEAF IS 0.0065-0.0100
- 6 - CORRESPONDS TO NASON PART NUMBER SM-1773

RELEASE NO.
PR - 22437

REPLACES
-

CHARACTERISTICS 4
OPERATING FORCE - - - -12 OZ MAX
RELEASE FORCE - - - - 2 OZ MIN
DIFFERENTIAL TRAVEL 5 - .005 MIN
OVERTRAVEL - - - - .011 MIN

ELECTRICAL DATA			
CONTACT ARRANGEMENT SPDT			
APPROVALS	KEMA, CE	11A 250V ~ T85 1E4 5A 30 Vdc T85 1E4	CE
	UL, CSA	11A 1/4 HP 125 250 VAC 5A 30 VDC	BRAND L190

DESIGN UNITS: INCH			
TOLERANCES UNLESS NOTED:			
NO PLACE	X	±	0.030
ONE PLACE	.X	±	0.015
TWO PLACE	.XX	±	0.005
THREE PLACE	.XXX	±	-
FOUR PLACE	.XXXX	±	-
ANGLES		±	-
THIRD ANGLE PROJECTION			

DRAWN	VK	30 OCT 07
CHECK	RJ	30 OCT 07
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

Honeywell			
TITLE SWITCH - BASIC			
SIZE B	TYPE I	DRAWING NAME 141SM32-H2	REV 3
SCALE -	WEIGHT .006 LB MAX	SHEET 1 OF 1	