


REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/02/11	D.N.



NOTES:

MATERIALS:

1. BODY & BACK NUT = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.
2. INSULATORS = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
3. CONTACT = BERYLLIUM COPPER PER ASTM B196, ALLOY C17300, TEMPER TD04.

FINISHES:

1. BODY & BACK NUT = GOLD PLATE PER MIL-G-45204, TYPE II, CLASS 0, GRADE C, OVER .00010 TO .00020 COPPER STRIKE PER MIL-C-14550.
2. CONTACT = GOLD PLATE PER MIL-G-45204, TYPE II, CLASS 1, GRADE C, OVER .00010 TO .00020 STRESS FREE SULFAMATE NICKEL PER QQ-N-290.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		DWN:	DATE	 Property of Radiall This document cannot be reproduced or communicated to a third party without prior written permission of RADIALL.	
		D.N.	11/02/11		
DECIMAL	ANGLE	CHKD:	DATE	SSMC STRAIGHT JACK SOLDER TYPE FOR .085 S/R & SIMILAR CABLES	
		J.S.	11/02/11		
		APVD:	DATE	SIZE A FSCM NO. 19505 DWG NO. 7101-1541-010 REV A	
		J.M.	11/02/11		
REFERENCE:		MATERIALS & FINISHES:		THIRD ANGLE PROJECTION	
ORIGINATED: D.N. DATE: 11/02/11		SEE NOTES		SCALE 8:1  SHEET 1 OF 1	

7101-1541-010