

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


ALL RIGHTS RESERVED.

© COPYRIGHT - TE Connectivity

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	H1	REVISED PER ECR-17-013215	18SEP17	J.Z	D.Z

- ① 0.00381 MIN BRIGHT TIN LEAD PLATING ALL OVER.
- ② REED STRAIGHT TOOTH KNURL CS 80-80 T.P.I., 125 TEETH, 70° INCLUDED ANGLE. FITS 1.50 - 1.57 DIAMETER HOLE IN A 0.79 PRINTED CIRCUIT BOARD.
3. PARTS TO COMPLY WITH AMP SOLDERABILITY SPECIFICATION 109-11-3.
- ④ MATES WITH AMP PARTS 60354, 60598 OR 60804.
- ⑤ 0.00381 MIN BRIGHT TIN PLATING ALL OVER.




-	-
6.67	.263
4.18	.165
3.72	.146
2.79	.110
1.70	.067
1.57	.062
1.50	.059
1.47	.058
1.14	.045
0.79	.031
0.76	.030
0.51	.020
0.25	.010
0.13	.005
0.00381	.000150
MM	IN
CONVERSION TABLE	

METRIC

⑤	3-60839-1
⑤	60839-1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mmMATERIAL
BRASSTOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± 0.13
3 PLC	± -
4 PLC	± -
ANGLES	± -

FINISH
SEE TABLE

DWN	8-15-97
T. BECK	
CHK	8-15-97
R. SWING	
APVD	9-10-97
A. REDDICK	
PRODUCT SPEC	108-1025
APPLICATION SPEC	114-1008
WEIGHT	0.000000
CUSTOMER DRAWING	



TE Connectivity

NAME	PIN, .058 DIAMETER, BRASS, KNURLED, P.C. CONTACT			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
A3	00779	C-60839	-	
SCALE	10:1	SHEET	1 OF 1	REV H1