



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AJ	16		0	REV PER EC-0S14-0496-04	02FEB2005	LV	KW

D



PCB CONFIGURATION






C



FRONT
DIELECTRIC
(BLACK) 8

CONTACT 1/5

MIDDLE
DIELECTRIC 8



SUGGESTED PANEL CUTOUT

- 1 PHOSPHOR BRONZE PER QQ-B-750.
- 2 BRASS PER ASTM-B-453
- 3 ZINC PER QQ-Z-363.
- 4 ACETAL, GENERAL PURPOSE
- 5 TIN PLATE PER ASTM-B-545, 3.81 μm [.000150] MINIMUM THICK. NICKEL PLATE PER QQ-N-290 1.27 μm [.000050] MINIMUM THICK.
- 6 CONNECTOR WILL ACCEPT CENTER CONDUCTOR DIAMETER RANGE OF 0.56[.022]–1.19[.047]
- 7 RETURN LOSS: –20dB MIN AT 1 GHz.
- 8 POLYMETHYLPENTENE, GENERAL PURPOSE.
- 9 MAJOR DIA MODIFIED TO .365 REF.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.VARELA – DOCK5 02FEB2005		tyco <i>Electronics</i>		Tyco Electronics Corporation Harrisburg, Pa 17105–3608							
		CHK J. HAVENER 02FEB2005											
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K. WEIDNER 02FEB2005		NAME							
		0 PLC ± –		PRODUCT SPEC		JACK, PCB, RIGHT ANGLE, SEALED, F SERIES							
		1 PLC ± –		108–1800									
		2 PLC ± –		APPLICATION SPEC									
		3 PLC ± 0.20 [.008]		—		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
		4 PLC ± –				A2		00779		C-6274430		—	
		ANGLES ± –											
MATERIAL		FINISH		WEIGHT									
—		—		—									
CUSTOMER DRAWING						SCALE		5:1		SHEET		1 OF 1	
												REV 0	

6274430–1

PART
NUMBER