




P1 HEATSINK
MAT'L: 6063-T5 ALUMINUM (AAVID EXTRUSION #60840)
FINISH: ANODIZE PER MIL-A-8625, TYPE II, CL 2, BLACK
TYPICAL BREAKDOWN VOLTAGE > 300V

- NOTES:**
- UNLESS OTHERWISE NOTED, ALL DIMENSIONS ARE IN INCHES.
 - BREAK ALL SHARP EDGES, DE-BURR & REMOVE LOOSE CHIPS.
 - MARK WITH CONTRASTING INK AS SHOWN, IF SPECIFIED BY PURCHASE ORDER.

TOLERANCES - UNLESS OTHERWISE SPECIFIED		TITLE: MODULAR PACKAGE HEATSINK		MODEL: HS31	
.XX = ±.05 [.002]		SUBJECT: MECHANICAL DRAWING		ENGINEER: D-M	
.XXX = ±.005 [.0002]		DRAWN BY: P.ECK		DATE: 12436	
ANG. = ±2°		SHEET: 1 OF 1		REV: C	
APEX MICROTECHNOLOGY PRECISION POWER SOLUTIONS		FILENAME: HS31		DATE: 14NOV12	