

SPECIFICATIONS


(RoHS Compliant)



Model Number: TNE3A
Part Number: 19020172A
SPEN NUMBER: 26013845A01

Jan 24, 2013

Mechanical Drawing:



Suggested Mounting - Recommended cutout diameter in customer panel is 6.75
171.4

DIMENSIONS: in $\pm$
mm
TOLERANCES: .xx= .03
0.8
.xxx=.010
(UNLESS NOTED) .25

Specifications subject to change without notice.

Motor:

Frequency = 50/60 Hz
Nominal Voltage = 220/230 VAC
Nominal Running Current = 0.260 Amps
Max. Locked Rotor Current = 0.650 Amps
Running Power = 59 Watts
Average Speed = 3470 RPM
Bearings = Ball
Air Flow = 280/340 CFM
Acoustic = 61.6/65.4 dBA

Construction:

Venturi: Plastic, Black, UL 94V-0
Propeller & Cover: Plastic, Black, UL 94V-0

Life Expectancy:

This fan is designed for continuous duty life of 25,000 hours at 40°C.

Additional Features:

Permanent Split Capacitor Motor
Automatic Reset Thermal Protector
Locked Rotor Protection
Operating Temperature: -10°C to 70°C
Storage Temperature: -40°C to 85°C

Termination:

Two blade terminals

Agencies:

UL, CE