



DESCRIPTION: ECONOMY FLAT RIBBON CONNECTOR



	A	B	C
9	1.213	.984	.850
	30.89	24.99	21.50
15	1.541	1.312	.850
	39.14	33.32	21.50
25	2.090	1.852	.850
	53.09	47.04	21.50
37	2.732	2.500	.850
	69.39	63.50	21.50

186-XXX-192L001

SERIES _____
POSITIONS _____
009
015
025
037
050
GENDER _____
1 = MALE
2 = FEMALE
TERMINATION _____
9 = IDC
SHELL PLATING _____
2 = TIN
HARDWARE OPTIONS _____
00 = NO HARDWARE
55 = 4-40 INSERTS
PLATING OPTIONS _____
01 = GOLD FLASH

SPECIFICATIONS:

MATERIALS:

SHELL: STEEL, TIN PLATED
INSULATOR: UL 94V-0 RATED PBT
+30% FIBER-GLASS OR NYLON-66
CONTACTS: BRASS
RoHS COMPLIANT

ELECTRICALS:

CURRENT RATING: 1 AMP
CONTACT RESISTANCE: 15 mOHMS MAX
INSULTOR RESISTANCE: 1000 MOHMS MIN
VOLTAGE: 500V AC FOR 1 MINUTE
TEMPERATURE: -55°C TO +100°C

FOR USE WITH 26/28 AWG STRANDED .050 CENTER FLAT CABLE

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: WAYNE ROBBINS		DATE: 9-16-05	
		CHECKED:		DATE:	
NorComp		SCALE: 1:1	SHEET 1 OF 1		REV 1
		DWG NO. 186-XXX-192L551			