



2		1					
LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			F	REV PER ECO 14-10695	7-16-14	CT	DH
		</					



- 1 HOUSING: LCP, UL94V0, COLOR: BLACK. CONTACT: PHOSPHOR BRONZE.
- 2 FINISH: 1.27µm GOLD IN CONTACT AREA 1.27µm MIN TIN-LEAD ON PCB TAIL OVER 3.81µm MIN NICKEL OVER ALL.
- 3 FINISH: 1.27µm GOLD IN CONTACT AREA 1.27µm MIN TIN ON PCB TAIL OVER 3.81µm MIN NICKEL OVER ALL.
- 4 MANUFACTURING TOLERANCE FOR:
Ø0.56±0.05 FINISHED HOLE WITH Sn PB PLATING:
DRILLED HOLE = Ø0.65±0.02
COPPER PLATING = 0.025-0.050
Sn PB PLATING = 0.0038-0.0124
OR
Ø0.575±0.050 FINISHED HOLE WITHOUT Sn PB PLATING:
DRILLED HOLE = Ø0.65±0.02
COPPER PLATING = 0.025-0.050
- 5 ADDITIONAL CONNECTOR SIDE KEEPOUT AREA REQUIRED IF CONNECTOR SIDE EXTRACTION TOOL IS TO BE USED.
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 7 TE PART NO AND DATE CODE MARKED IN THIS AREA, EITHER SIDE

OBSOLETE	REMARKS	PLATING	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.5
1 PLC ±0.13
2 PLC ±0.13
3 PLC ±0.13
4 PLC ±0.13
ANGLES ±1°

FINISH

DWN R.TREA 27FEB2002
CHK J.CONSOLE 27FEB2002
APVD J.CONSOLE 27FEB2002

PRODUCT SPEC 108-2072
APPLICATION SPEC 114-13056

WEIGHT

CUSTOMER DRAWING

NAME

SIZE CAGE CODE DRAWING NO
A100779C=1410128

RESTRICTED TO

TE Connectivity

CONNECTOR ASSEMBLY, BACKPLANE VERTICAL RECEPTACLE, RIGHT END, 25.4mm, MultiGig RT 2

SCALE 8:1 SHEET 1 OF 1 REV F