

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - "Specific": Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

M61509FP

QXpander built-in, Tone control, Volume control

REJ03F0215-0201

Rev.2.01

Mar 31, 2008

Description

The M61509FP is the sound controller powered by “QXpander” system.

The “QXpander” system produces normal and wide 3D sound expansion from any stereo input signal.

Note: This device is produced under license from QSound Lab, Ins. (Canada)

Features

- Built-in “QXpander” sound technology
- Electronic volume.
0 to -84 dB, the infinitesimal.
- 2-band tone control
Bass (0 to +21 dB/3 dB STEP)
Treble (0 to +9 dB/3 dB STEP)
- 5input selector (The fifth input can be used as REC OUT or MIC MIX.)


Recommended Operating Condition

Supply voltage range: ± 2.25 to ± 2.75 V


Application

Radio Cassette Recorders, Mini-stereo Set, Audio Equipment

System Block Diagram



Block Diagram



Pin Function Description


Pin No.	Name	Function
1	IN A1	INPUTs of the channel 1 The switch of INE can be controlled in dependently. Please set "ALL OFF" mode when the switch of E is only ON.
2	IN B1	
3	IN C1	
4	IN D1	
5	IN E1	
6	QF1	QXpander filter 1
7	QF2	QXpander filter 2
8	TONEH1	Treble control adjustment of the channel 1
9	TONEL1	Bass control adjustment of the channel 1
10	OUT1	OUTPUT of the channel 1
11	GND	Ground
12	VDD	Supply voltage (+)
13	CONT	Control data input from a microcontroller
14	VSS	Supply voltage (-)
15	OUT2	OUTPUT of the channel 2
16	TONEL2	Bass control adjustment of the channel 2
17	TONEH2	Treble control adjustment of the channel 2
18	QF3	QXpander filter 3
19	QF4	QXpander filter 4
20	IN E2	INPUTs of the channel 2 The switch of INE can be controlled independently. Please set "ALL OFF" mode when the switch of E is only ON.
21	IN D2	
22	IN C2	
23	IN B2	
24	IN A2	

Absolute Maximum Ratings

(Ta = 25°C, unless otherwise noted)

Item	Symbol	Ratings	Unit	Test Condition
Supply voltage	VDD-VSS	6.0	V	
Thermal derating	Kθ	5	mW/°C	(Note)
Power dissipation	Pd	500	mW	
Operating temperature	Topr	–20 to 75	°C	
Storage temperature	Tstg	–40 to 125	°C	

Note: reference PC Board
 Size: 70 mm × 70 mm
 Thickness: 1.6 mm
 Material: glass epoxy
 Copper pattern dimension
 Width: 0.25 mm
 Length: 25 to 30 mm/lead
 Thickness: 18 μm




Recommended Operating Conditions

Item	Symbol	Pin No.	Limits			Unit	Condition
			Min	Typ	Max		
Supply voltage (+)	VDD	12	2.25	2.5	2.75	V	
Supply voltage (–)	VSS	14	–2.75	–2.5	–2.25		
Control data input voltage	CONT	13	GND	—	VDD		

Control Signals Specification

(1) Wave Form



(2) Voltage Control Signal

Digital input signal		Limits			Unit	Condition
		Min	Typ	Max		
L signal	L	GND	—	0.4	V	VDD = 2.5 V, VSS = -2.5 V
M signal	M	1.0	1.25 (VDD/2)	1.5		VDD = 2.5 V, VSS = -2.5 V
H signal	H	2.1	—	VDD		VDD = 2.5 V, VSS = -2.5 V


(3) Timing Control Signal

Item	Symbol	Limits			Unit
		Min	Typ	Max	
Cycle time of digital signal	t_{cr}	8	—	—	μ s
Pulse width of digital signal ("H" level)	t_{WH}	3.6	—	—	
Pulse width of digital signal ("L" level)	t_{WLC}	3.6	—	—	
Rise time of digital signal	t_r	—	—	0.4	
Fall time of digital signal	t_f	—	—	0.4	

(4) Control Signal Example (Refer to the "Control Data Format")

An example of the mode control

- Bypass/QXpander SW: QXpander
- VOL/Treble Share AMP Gain: 20 dB
- Input: IN A,
- Volume: 0 dB
- Mute: OFF
- Mode: STEREO
- Bass: 18 dB
- Treble: 6 dB
- Recout: ON (IN E)



Control Data Format

It is necessary to set up the all control data after power on.

(1) Input Data

(MSB) ← input order

Slot1

D01	D11	D21	D31	D41	D51	D61	D71	D81	D91	D101	D111	D121	D131
0	Bypass/QXpander SW	Vol/Treble share amp gain SW 0: 20 dB 1: 18 dB 2: 16 dB 3: 14 dB		Input 0: IN A 1: IN B 2: IN C 3: IN D		D2 to D6: (a) Master volume condition					Mute ON/OFF 0: OFF 1: ON (Input ALL OFF)	CHIP/SLOT Select 0: select 1: no select 2: no select 3: no select	

Slot2

D02	D12	D22	D32	D42	D52	D62	D72	D82	D92	D102	D112	D122	D132
1	1	0	1	Mode select 0: stereo 1: mono1 only 2: mono2 only 3: mono 1+2		Bass (boost) 0: 0 dB, 1: 3 dB, 2: 6 dB, 3: 9 dB, 4: 12 dB, 5: 15 dB, 6: 18 dB, 7: 21 dB			Treble (boost) 0: 0 dB, 1: 3 dB, 2: 6 dB, 3: 9 dB		IN E ON/OFF 0: OFF 1: ON	CHIP/SLOT Select 0: no select 1: no select 2: no select 3: select	

(a) Master Volume

ATT	D61	D71	D81	D91	D101
-0.0 dB	0	0	0	0	0
-2.0 dB	1	0	0	0	0
-4.0 dB	0	1	0	0	0
-6.0 dB	1	1	0	0	0
-8.0 dB	0	0	1	0	0
-10.0 dB	1	0	1	0	0
-12.0 dB	0	1	1	0	0
-14.0 dB	1	1	1	0	0
-16.0 dB	0	0	0	1	0
-18.0 dB	1	0	0	1	0
-20.0 dB	0	1	0	1	0
-22.0 dB	1	1	0	1	0
-24.0 dB	0	0	1	1	0
-26.0 dB	1	0	1	1	0
-28.0 dB	0	1	1	1	0
-30.0 dB	1	1	1	1	0
-32.0 dB	0	0	0	0	1
-34.0 dB	1	0	0	0	1
-36.0 dB	0	1	0	0	1
-40.0 dB	1	1	0	0	1
-44.0 dB	0	0	1	0	1
-48.0 dB	1	0	1	0	1
-52.0 dB	0	1	1	0	1
-56.0 dB	1	1	1	0	1
-60.0 dB	0	0	0	1	1
-64.0 dB	1	0	0	1	1
-68.0 dB	0	1	0	1	1
-72.0 dB	1	1	0	1	1
-76.0 dB	0	0	1	1	1
-80.0 dB	1	0	1	1	1
-84.0 dB	0	1	1	1	1
The infinitesimal	1	1	1	1	1

(b) Input Select

Input select		D41	D51	D111	D112
IN A	IN E off	0	0	0	0
IN B		1	0		
IN C		0	1		
IN D		1	1		
IN A to D all OFF	IN E on	*	*	1	1 (Note 1)
IN A-D select		A: 0	0	0	1 (Note 2)
		B: 1	0		
		C: 0	1		
		D: 1	1		

Notes: 1. The input impedance is about 5 k as input IN E.

2. IN E can be controlled independently.

It can be used as Rec output.

(c) Mode Control

Mode	D42	D52
stereo	0	0
mono 1 only	1	0
mono 2 only	0	1
mono 1+2	1	1

(d) Treble Control

Treble	D92	D102
0 dB	0	0
3 dB	1	0
6 dB	0	1
9 dB	1	1

(e) Bass Control

Bass	D62	D72	D82
0 dB	0	0	0
3 dB	1	0	0
6 dB	0	1	0
9 dB	1	1	0
12 dB	0	0	1
15 dB	1	0	1
18 dB	0	1	1
21 dB	1	1	1

(f) Chip/Slot Control

Chip/Slot	D12*	D13*
select (slot1)	0	0
no select	1	0
no select	0	1
select (slot1)	1	1

(g) Treble Amp Gain SW

Gain SW	D21	D31
20 dB	0	0
18 dB	1	0
16 dB	0	1
14 dB	1	1

(h) Bypass/QXpander SW

Bypass/QXpander SW	D11
Bypass	0
QXpander	1

(2) Notice of Control Data

1. use only the control data of (1) Input Data.
2. The interval of data transmission from the microcontroller is over 0.1 s.
: This is the waiting time for the “soft-switching” to reduce the shock noise. (The “soft-switching” is available at the volume and QXpander.)

Note:

- (1) The “Slot1” and the “Slot2” are independent data.

Each data need each waiting time.

- (2) The some function of the volume and other function have no “soft-switching”.

Example1:

When the volume is set as “infinitesimal”, it's immediately attenuated (but, it needs the waiting time to reach the final attenuation).

Example2:

The change of tone control is immediately executed.

3. It is necessary to set the all control data after power-on, although the internal circuit is forced as below, when (VDD-VSS) ≤ 3.3 V (Typ).

Item	Condition
Gain SW	18 dB
Input select	ALL OFF
Master volume	infinitesimal
MUTE	ON (Input ALL OFF)
Bypass/QXpander	Bypass
Mode select	stereo
Bass	0 dB
Treble	0 dB
IN E	ON


Electrical Characteristics

(VDD = 2.5 V, VSS = -2.5 V, f = 1 kHz, Vi = 100 mV(rms), Vol = 0 dB, Bass = 0 dB, Treble = 0 dB, Vol/Treble Share AMP = 18 dB, Surround = Bypass, RL = 10 kΩ, Ta = 25°C, unless otherwise noted)

Item	Symbol	Limits			Unit	Conditions	
		Min	Typ	Max			
Circuit current of positive power supply	IDD	—	30	45	mA	Quiescent	
Circuit current of negative power supply	ISS	—	-30	-45	mA	Quiescent	
Voltage gain (selector)	Gv1	16	18	20	dB	Vol/Treble share amp gain = 18 dB Bypass	
Voltage gain (tone control)	Gv2	25.5	27.5	29.5	dB	Vol/Treble share amp gain = 18 dB QXpander mode Vi = 20 mVrms	
Maximum output voltage	Vomax	1.2	1.6	—	Vrms	RL = 10 k, THD = 1%	
Total harmonic distortion	THD	—	0.02	0.08	%	BW = 400 to 30 kHz	
Output noise voltage	No1	—	6	15	μVrms	JIS-A, Rg = 5.1 k, VOL = the infinitesimal BYPASS	
	No2	—	11	30	μVrms	JIS-A, Rg = 5.1 k, VOL = the infinitesimal QXpander mode	
Maximum attenuation	ATTmax	—	-95	-90	dB	Output reference level (Vo = 1 Vrms), ATT = the infinitesimal, JIS-A	
Bass boost	GB1	1.5	3	4.5	dB	3 dB	f = 1 kHz, Vo = 80 mVrms
	GB2	4.5	6	7.5		6 dB	
	GB3	7.5	9	10.5		9 dB	
	GB4	10.5	12	13.5		12 dB	
	GB5	13.5	15	16.5		15 dB	
	GB6	16.5	18	19.5		18 dB	
	GB7	19.5	21	22.5		21 dB	
Treble boost	GT1	1.5	3	4.5		3 dB	f = 1 kHz, Vo = 80 mVrms
	GT2	4.5	6	7.5		6 dB	
	GT3	7.5	9	10.5		9 dB	

Function Description


(1) Equivalent Circuit of the Bass Boost



R2, R3 (typical)

Bass boost		3 dB	6 dB	9 dB	12 dB	15 dB	18 dB	21 dB
Resistor (k)	R2	15.4	25.7	32.9	38.7	41.6	44.2	46
	R3	30.6	20.3	13.1	7.3	4.4	1.8	0

(2) Equivalent Circuit of the Treble Boost




R2 (typical)

Treble boost	3 dB	6 dB	9 dB
R2 (k)	5.3	2.2	1.2


R1, R3 (typical)

Gain	14 dB	16 dB	18 dB	20 dB
R1 (k)	10.88	13.65	17.21	21.60
R3 (k)	2.72	2.57	2.48	2.40

Application Example



Package Dimensions



Notes:

1. This document is provided for reference purposes only so that Renesas customers may select the appropriate Renesas products for their use. Renesas neither makes warranties or representations with respect to the accuracy or completeness of the information contained in this document nor grants any license to any intellectual property rights or any other rights of Renesas or any third party with respect to the information in this document.
2. Renesas shall have no liability for damages or infringement of any intellectual property or other rights arising out of the use of any information in this document, including, but not limited to, product data, diagrams, charts, programs, algorithms, and application circuit examples.
3. You should not use the products or the technology described in this document for the purpose of military applications such as the development of weapons of mass destruction or for the purpose of any other military use. When exporting the products or technology described herein, you should follow the applicable export control laws and regulations, and procedures required by such laws and regulations.
4. All information included in this document such as product data, diagrams, charts, programs, algorithms, and application circuit examples, is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas products listed in this document, please confirm the latest product information with a Renesas sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas such as that disclosed through our website. (<http://www.renesas.com>)
5. Renesas has used reasonable care in compiling the information included in this document, but Renesas assumes no liability whatsoever for any damages incurred as a result of errors or omissions in the information included in this document.
6. When using or otherwise relying on the information in this document, you should evaluate the information in light of the total system before deciding about the applicability of such information to the intended application. Renesas makes no representations, warranties or guarantees regarding the suitability of its products for any particular application and specifically disclaims any liability arising out of the application and use of the information in this document or Renesas products.
7. With the exception of products specified by Renesas as suitable for automobile applications, Renesas products are not designed, manufactured or tested for applications or otherwise in systems the failure or malfunction of which may cause a direct threat to human life or create a risk of human injury or which require especially high quality and reliability such as safety systems, or equipment or systems for transportation and traffic, healthcare, combustion control, aerospace and aeronautics, nuclear power, or undersea communication transmission. If you are considering the use of our products for such purposes, please contact a Renesas sales office beforehand. Renesas shall have no liability for damages arising out of the uses set forth above.
8. Notwithstanding the preceding paragraph, you should not use Renesas products for the purposes listed below:
 - (1) artificial life support devices or systems
 - (2) surgical implantations
 - (3) healthcare intervention (e.g., excision, administration of medication, etc.)
 - (4) any other purposes that pose a direct threat to human lifeRenesas shall have no liability for damages arising out of the uses set forth in the above and purchasers who elect to use Renesas products in any of the foregoing applications shall indemnify and hold harmless Renesas Technology Corp., its affiliated companies and their officers, directors, and employees against any and all damages arising out of such applications.
9. You should use the products described herein within the range specified by Renesas, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas shall have no liability for malfunctions or damages arising out of the use of Renesas products beyond such specified ranges.
10. Although Renesas endeavors to improve the quality and reliability of its products, IC products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Please be sure to implement safety measures to guard against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other applicable measures. Among others, since the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
11. In case Renesas products listed in this document are detached from the products to which the Renesas products are attached or affixed, the risk of accident such as swallowing by infants and small children is very high. You should implement safety measures so that Renesas products may not be easily detached from your products. Renesas shall have no liability for damages arising out of such detachment.
12. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written approval from Renesas.
13. Please contact a Renesas sales office if you have any questions regarding the information contained in this document, Renesas semiconductor products, or if you have any other inquiries.



RENESAS SALES OFFICES

<http://www.renesas.com>

Refer to "<http://www.renesas.com/en/network>" for the latest and detailed information.

Renesas Technology America, Inc.
450 Holger Way, San Jose, CA 95134-1368, U.S.A
Tel: <1> (408) 382-7500, Fax: <1> (408) 382-7501

Renesas Technology Europe Limited
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K.
Tel: <44> (1628) 585-100, Fax: <44> (1628) 585-900

Renesas Technology (Shanghai) Co., Ltd.
Unit 204, 205, AZIA Center, No.1233 Lujiazui Ring Rd, Pudong District, Shanghai, China 200120
Tel: <86> (21) 5877-1818, Fax: <86> (21) 6887-7858/7898

Renesas Technology Hong Kong Ltd.
7th Floor, North Tower, World Finance Centre, Harbour City, Canton Road, Tsimshatsui, Kowloon, Hong Kong
Tel: <852> 2265-6688, Fax: <852> 2377-3473

Renesas Technology Taiwan Co., Ltd.
10th Floor, No.99, Fushing North Road, Taipei, Taiwan
Tel: <886> (2) 2715-2888, Fax: <886> (2) 3518-3399

Renesas Technology Singapore Pte. Ltd.
1 Harbour Front Avenue, #06-10, Keppel Bay Tower, Singapore 098632
Tel: <65> 6213-0200, Fax: <65> 6278-8001

Renesas Technology Korea Co., Ltd.
Kukje Center Bldg. 18th Fl., 191, 2-ka, Hangang-ro, Yongsan-ku, Seoul 140-702, Korea
Tel: <82> (2) 796-3115, Fax: <82> (2) 796-2145

Renesas Technology Malaysia Sdn. Bhd
Unit 906, Block B, Menara Amcorp, Amcorp Trade Centre, No.18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia
Tel: <603> 7955-9390, Fax: <603> 7955-9510