


	10	9	8	7	6	5	4	3	2	19127					
	LOOSE PIECE		TAPE MOUNTED		DIMENSIONS										FINISH
	MATERIAL NUMBER	ENGINEERING NUMBER	MATERIAL NUMBER	ENGINEERING NUMBER	STUD SIZE	S ±.005	W MAX	C MIN	ID MIN	MWID	B REF	L MAX	H REF	T REF	INSULATION COLOR
F	191270007	AA-815-06	191270009	AA-815-06T	6	.146/3.71	.301/7.6	.207/5.3	.054/1.37	.138/3.51	.400/10.16	.781/19.84	.08/2.0	.031/0.79	RED
	191270010	AA-815-08	191270011	AA-815-08T	8	.173/4.39	.301/7.6	.207/5.3	.054/1.37	.138/3.51	.400/10.16	.781/19.84	.08/2.0	.031/0.79	RED
	191270012	AA-815-10	191270013	AA-815-10T	10	.198/5.03	.301/7.6	.207/5.3	.054/1.37	.138/3.51	.400/10.16	.781/19.84	.08/2.0	.031/0.79	RED
	191270039	BB-816-06	191270041	BB-816-06T	6	.146/3.71	.301/7.6	.209/5.3	.081/2.06	.165/4.19	.400/10.16	.810/20.32	.08/2.0	.031/0.79	BLUE
	191270042	BB-816-08	191270044	BB-816-08T	8	.173/4.39	.301/7.6	.209/5.3	.081/2.06	.165/4.19	.400/10.16	.810/20.32	.08/2.0	.031/0.79	BLUE
	191270099	BB-816-10	191270045	BB-816-10T	10	.198/5.03	.301/7.6	.209/5.3	.081/2.06	.165/4.19	.400/10.16	.810/20.32	.08/2.0	.031/0.79	BLUE
E	191270083	C-817-06	191270084	C-817-06T	6	.146/3.71	.345/8.8 (A)	.270/6.85 (A)	.128/3.25	.225/5.71	.560/14.22	1.026/26.1 (A)	.10/2.5	.040/1.02	YELLOW
	191270086	C-817-08	191270087	C-817-08T	8	.173/4.39	.385/9.8	.270/6.85 (A)	.128/3.25	.225/5.71	.560/14.22	1.026/26.1 (A)	.10/2.5	.040/1.02	YELLOW
	191270089	C-817-10	191270090	C-817-10T	10	.209/5.3 (A)	.385/9.8	.270/6.85 (A)	.128/3.25	.225/5.71	.560/14.22	1.026/26.1 (A)	.10/2.5	.040/1.02	YELLOW



A	NOTES: 1. MATERIAL: COPPER 2. PLATING: ELECTRO-TIN 3. MWID = MAXIMUM WIRE INSULATION DIAMETER 4. PART IS RoHS COMPLIANT				12-10 TO ALT DIE DIMS EC NO: ETC2008-0012 DRWN: RSTONE 2007/11/26 CHKD: JACNEIL 2007/11/26 APPR: JACNEIL 2007/12/05				REV B	DESCRIPTION ▽=0 ∇=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM			SCALE 4:1		DESIGN UNITS INCH		THIRD ANGLE PROJECTION	
					4 PLACES ± --- ± ---		mm				INCH		DRAWN BY DATE DLM 2003/08/25		TITLE FLANGED SPADE TERMINAL, AVIKRIMP -800 SERIES							
					3 PLACES ± --- ± .005						CHECKED BY DATE HEB 2003/08/25											
					2 PLACES ± 0.13 ± .01						APPROVED BY DATE RWD 2003/08/25											
		1 PLACE ± 0.25 ± ---				ANGULAR ± 1/2°		MATERIAL NO. SEE CHART		DOCUMENT NO. SD-19127-003				SHEET NO. 1 OF 1								
						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
1b_frame_B_P_ME_T Rev. E 2006/04/15		9		8		7		6		5		4		3		2		1				