



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		J	REVISED PER ECR-12-013518	23NOV2012	KH	PD


- 1
- CONTINUOUS STRIP ON REELS.
- 2
- MATING TAB THK TO BE 0.508±0.025
[.020±.001]
- 3
- WIRE SIZE IS #18-#14 AWG.
- 4
- INSULATION RANGE IS 1.52-3.81
[.060-.150] DIA.
- 5
- RECEPTACLE LENGTH CAN BE GREATER
BY UP TO 0.25 [.010] MAX FROM
THE OPPOSITE SIDE.





VIEW A-A



SECTION B-B




SECTION C-C



PART NO	WIRE		INSULATION DIAMETER (MAX)	WIRE BARREL CRIMP				TENSILE STRENGTH POUNDS
	QTY	SIZE AWG		WIDTH	CRIMP HEIGHT	CRIMPER	ANVIL	
63512-1	1	14	.150	.120	.071	F	FLAT	50
	1	16			.063			30
	1	18			.057			20

OBSOLETE		.000080 MIN TIN	63512-4
OBSOLETE	REVERSE REELING		63512-3
		-	63512-1
	REELING	FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 9/29/88		 TE Connectivity			
		CHK MS FEHER 9/30/88					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE, FLAG, FASTON, 4.75 [.187] SERIES —		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
		APVD C MEYERS 9/30/88					
		PRODUCT SPEC —					
		APPLICATION SPEC —					
MATERIAL BRASS		FINISH SEE TABLE		WEIGHT —		A2 00779 C-63512	
CUSTOMER DRAWING				SCALE 4:1		SHEET 1 of 1	
				REV J			