

PRODUCT NUMBER
91618-YXXZLF

RoHS COMPATIBLE, SEE NOTE 7

A: PRODUCT WITH PICK UP CAP PACKED IN
TAPE & REEL SEE TA856.

B: PRODUCT WITH PICK UP CAP PACKED IN TUBE.

NUMBER OF POSITIONS PER ROW: 06 UP TO 30.
MORE THAN 30 POSITIONS ON SPECIAL REQUEST.

3= 0.76µm GOLD ON CONTACT AREA.
2µm MIN MATTE TIN ON TAIL.

4= 2µm TIN FULL PLATED

8= 0.38µm GOLD ON CONTACT AREA.
2µm MIN MATTE TIN ON TAIL.

1.27µm Ni MIN UNDERPLATING

NOTES:

- 1 - HOUSING MAT'L: THERMOPLASTIC GLASS FILLED
FLAME RETARDANT PER UL 94 V-0 COLOR: GREY.
- 2 - TERMINAL MATERIAL: PHOSPHOR BRONZE.
- 3 - 06 UP TO 30 POSITIONS PRODUCT PACKED IN TUBE.
- 4 - TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS PER ROW
EXAMPLE: 8 POS: $(N \times 2.54) - 0.08 = 20.24$ mm.
- 5 - RECOMMENDED IR PROFILE PER TA842.
- 6 - Ø2.65 MINI FOR PICK & PLACE ASSEMBLY(=0 INSERTION FORCE).
- 7 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - PLATING:

- "LF" MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.

b - MANUFACTURING PROCESS COMPATIBILITY


- THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C PEAK TEMPERATURE FOR 30 SECONDS
MAX IN A CONVECTION, INFRA-RED OR VAPOR
PHASE OR REFLOW OVEN.

c - LABELING:


- MEETS PACKAGING SPECS AS PER GS-14-920

d - LEGAL STATEMENT: SEE GS-47-0004

8 - NO END STAND-OFFS



mat'l. code SEE NOTES				surface ISO 1302	tolerance ISO 406 ISO 1101	projection mm	product family DUBOX			
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title			
W	F-21499	AMA	15.07.23	angles	linear		BtB RECEPT.			
R	F04-0347	DLE	04.11.10	±2°		scale 5/1	VERT DR SMT			
S	F06-0137	DLE	06.02.27	dr	D LEGRAND	02.10.08	FCI	dwg no		sheet 1 of 2
T	F06-0204	DLE	06.06.23	engr	P NIZZI	02.10.08		91618		size A3
U	F11-0043	JCO	12.02.22	chr	JF NOTTEAU	02.10.08		type		CUSTOMER Drawing
V	B-19123	LMU	14.10.21	appd	P NZ	02.10.08				
sheet	revision	W	B							
index	sheet	1	2							



Copyright FCI

mat'l. code SEE NOTES				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family DUBOX			
ltr	ecn no	dr	date	tolerances unless otherwise specified						title			
A	F04-0347	DLE	04.11.10	angles	linear	±0.3			BtB RECEPT. VERT DR SMT				
B	F06-0204	DLE	06.06.23			±2'						scale 5/1	
				dr	P LEGRAND	04.11.10			dwg no		sheet 2 of -	size	
				enr	P NIZZI	04.11.10			91618		A4		
				chr	D LEGRAND	04.11.10			type		CUSTOMER	Drawing	
				appd	P NZ	04.11.10							
sheet index		revision sheet											

form: A4