

SPECIFICATIONS

Mechanical

Operating Force & Durability: 100±30gf 1000000 Cycles
 160±50gf 1000000 Cycles
 260±80gf 100000 Cycles

Travel: 0.25+0.2/-0.1mm

Return Force: 25gf min.

Electrical

Rating: 50mA max.

Contact Resistance: 100mW max.

Insulation Resistance: 100MW min.

Dielectric Withstanding Voltage: 250V AC for 1 Minute

Bounce: 5ms max.


Physical

Operating Temperature: -20℃ to +70℃


Tact Switch

1BT003 Series

L SMT Type



DRAWING



ORDERING INFORMATION

PRODUCT NO.: 1BT003-2 ** 0 * - ** *

Switch Series ————
 Tact Type ————
 Product Series ————
 Prod. Size: 2=6.0mm*6.0mm ————
 Total Height ————
 5=4.3mm
 6=5.0mm
 7=7.0mm

Modification Code
 None=w/o Ground
 001=w/ Ground

Plating:
 0=Standard

Terminal:
 0=L SMT

Operating Force:
 1=100gf
 2=160gf

1BT003-25100-***	100±30gf	4.3
1BT003-25200-***	160±50gf	4.3
1BT003-25300-***	260±80gf	4.3
1BT003-26100-***	100±30gf	5.0
1BT003-26200-***	160±50gf	5.0
1BT003-26300-***	260±80gf	5.0
1BT003-27100-***	100±30gf	7.0
1BT003-27200-***	160±50gf	7.0
1BT003-27300-***	260±80gf	7.0
P/N	OPERATING FORCE	DIM. A