

(2.54 mm) .100"

**BBS, BBL, BHS, BBD, BDL SERIES**

MACHINED BOARD STACKING STRIPS

Mates with:SS, SD, HSS, SL, SDL,
ESS, ESD**FEATURES**

- Low-profile design achieves (3.89 mm) .153" board spacings when mated with SL Series.
- Approach the reliability of a permanent connection with the flexibility of a separable connection.

SPECIFICATIONS**Insulator Material:**

Black Glass Filled Polyester (BBS, BBD, BBL)

Black High Temp Nylon (BDL)

Black Liquid Crystal Polymer (BHS)

Temperature Range:

-55 °C to +125 °C

Terminal Material:

Phosphor Bronze or Brass

Plating:

Au or Sn over 50 µ" (1.27 µm) Ni

RoHS Compliant:

Yes

Lead-Free Solderable:

Wave only




(BBS, BBD, BBL, BDL)

Wave, or reflow with

all Au (BHS)

RECOGNITIONS**Note:**

Some lengths, styles and options are non-standard, non-returnable.



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.TOBY.CO.UK

All parts within this catalog are built to Samtec's specifications.

Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.