





DESCRIPTION: ABOVE AND BELOW P.C.B., DECK IS AS VIEWED BY USER.

PRODUCT NO. 72306-XXX	STAND-OFF HEIGHT DIM L	Ⓐ CLOSEST TO P.C.B. HEADER ASSY 72305-XXX	Ⓑ FARTEST FROM P.C.B. HEADER ASSY 72305-XXX	Ⓒ MATING RECEPTACLE	MOUNTING STYLE TO PCB
000	0.0	000	005	100 POSITION (2x50) 0.8mm RECEPTACLE PART NO. 73277-101000 ORDER SEPARATELY	
020	2.2	020	025		
040	4.3	040	045		
050	5.0	050	055		
520	2.2	520	525		
540	4.3	540	545		
550	5.0	550	555		
000LF	0.0	000LF	005LF	100 POSITION (2x50) 0.8mm RECEPTACLE PART NO. 73277-101000LF ORDER SEPARATELY	
020LF	2.2	020LF	025LF		
040LF	4.3	040LF	045LF		
050LF	5.0	050LF	055LF		
520LF	2.2	520LF	525LF		
540LF	4.3	540LF	545LF		
550LF	5.0	550LF	555LF		

NOTE:

1. SEE 72305 FOR SINGLE DECK APPLICATIONS

ORDERING INFORMATION



ORDER:

1. Ⓐ DECK CLOSEST TO P.C.B.
2. Ⓑ DECK FARTEST FROM P.C.B.
3. Ⓒ 2 EACH MATING RECEPTACLES

mat'l. code		surface ISO1302		tolerance ISO1101 ISO406		projection		product family MCS	
ltr ecn nodr		date		tolerances unless otherwise specified		MM		title	
D	V02257	TFG	11/3/00	angle	0.X±0.3	scale 1:1		CARDBUS DOUBLE DECK	
E	N05-0165	WB	06/15/06	0°±2'	0.XX±0.13			ASS'Y SMT TYPE 123	
F	EX-N-011410	ZK	04/02/12		0.XXX±0.051			dwg no	
				dr	R.GRAPE	9/9/96			sheet 1 of 9
				engr	D.BRANN	9/9/96			size
				chr	D.BRANN	9/9/96			A4
				appd	D.BRANN	9/9/96			type
								Product Customer Drawing	
sheet	revision	F	F	F	F	F	F	F	
index	sheet	1	2	3	4	5	6	7	8


PRODUCT NUMBER

72306-***/**LF








mat'l. code	surface	tolerance	projection	product family
	ISO1302	ISO1101 ISO406		MCS
ltr ecn nodr date	tolerances unless otherwise specified			title
F	angle	0.X±0.3	MM	CARDBUS DOUBLE DECK
		0.XX±0.13		ASS'Y SMT TYPE 123
	0°±2'	0.XXX±0.051	scale 1:1	
dr	R.GRAPE	9/9/96	FCI	dwg no
engr	D.BRANN	9/9/96		sheet 2 of 9
chr	D.BRANN	9/9/96		size
appd	D.BRANN	9/9/96		A4
sheet index	revision sheet			type Product Customer Drawing

PRODUCT NUMBER
72306-***/**LF



MATING RECEPTACLE SHOWN
FOR APPLICATION CLARITY ONLY.
MUST BE ORDERED SEPARATELY




P/N: 72306-020
P/N: 72306-020LF
ABOVE P.C.B.
PCB LAYOUT 3 (SH.7)

P/N: 72306-520
P/N: 72306-520LF
BELOW P.C.B.
PCB LAYOUT 4 (SH.7)




mat'l. code				surface		tolerance		projection		product family											
				ISO1302 ✓		ISO1101 ISO406				MCS											
ltr		ecn		nodr		date		tolerances unless otherwise specified		title											
F								angle		0.X±0.3				CARDBUS DOUBLE DECK ASS'Y SMT TYPE 123							
								0.XX±0.13													
								0°±2'		0.XXX±0.051											
								line		scale 1:1											
						dr		R.GRAPE		9/9/96				dwg no		sheet3 of 9		size			
						engr		D.BRANN		9/9/96				72306		A4					
						chr		D.BRANN		9/9/96											
						appd		D.BRANN		9/9/96											
sheet		revision												type		Product		Customer		Drawing	
index		sheet																			

PRODUCT NUMBER

72306-***/**LF




MATING RECEPTACLE SHOWN
FOR APPLICATION CLARITY ONLY.
MUST BE ORDERED SEPARATELY






mat'l. code	surface	tolerance	projection	product family
ISO1302	ISO1101	ISO406	MM	MCS
date	tolerances unless otherwise specified	angle	scale 1:1	title
F	0.X±0.3	0°±2'	MM	CARDBUS DOUBLE DECK
	0.XX±0.13			ASS'Y SMT TYPE 123
	0.XXX±0.051			
dr	R.GRAPE	9/9/96		dwg no
enr	D.BRANN	9/9/96		sheet 4 of 9
chr	D.BRANN	9/9/96		size
appd	D.BRANN	9/9/96		A4
sheet index	revision sheet			type Product Customer Drawing

PRODUCT NUMBER

72306-***/**LF




MATING RECEPTACLE SHOWN
FOR APPLICATION CLARITY ONLY.
MUST BE ORDERED SEPARATELY




mat'l. code	surface	tolerance	projection	product family
ISO1302	ISO1101	ISO406	MM	MCS
date	tolerances unless otherwise specified	angle	scale 1:1	title
F	0.X±0.3	0°±2'	MM	CARDBUS DOUBLE DECK
	0.XX±0.13			ASS'Y SMT TYPE 123
	0.XXX±0.051			
dr	R.GRAPE	9/9/96		dwg no
enr	D.BRANN	9/9/96		sheet 5 of 9
chr	D.BRANN	9/9/96		size
appd	D.BRANN	9/9/96		A4
sheet index	revision sheet			type Product Customer Drawing

P.C.B. LAYOUT FOR 2.2mm STANDOFF



mat'l. code				surface		tolerance		projection		product family											
				ISO1302 ✓		ISO1101 ISO406				MCS											
ltr		ecn		nodr		date		tolerances unless otherwise specified		title											
F								angle		0.X±0.3				CARDBUS DOUBLE DECK ASS'Y SMT TYPE 123							
								0.XX±0.13													
								0°±2'		0.XXX±0.051											
								line		scale 1:1											
						dr		R.GRAPE		9/9/96				dwg no		sheet 7 of 9		size			
						engr		D.BRANN		9/9/96				72306		A4					
						chr		D.BRANN		9/9/96											
						appd		D.BRANN		9/9/96											
sheet		revision												type		Product		Customer		Drawing	
index		sheet																			

P.C.B. LAYOUT FOR 4.3 AND 5.0mm STANDOFFS



mat'l. code				surface		tolerance		projection		product family							
				ISO1302 ✓		ISO1101 ISO406				MCS							
ltr		ecn		nodr		date		tolerances unless otherwise specified		title							
F								angle		0.X±0.3				CARDBUS DOUBLE DECK ASS'Y SMT TYPE 123			
								0.XX±0.13									
								0°±2'		0.XXX±0.051							
								line out		scale 1:1							
						dr		R.GRAPE		9/9/96		dwg no		sheet 8 of 9		size	
						engr		D.BRANN		9/9/96				72306		A4	
						chr		D.BRANN		9/9/96							
						appd		D.BRANN		9/9/96							
sheet		revision										type		Product Customer Drawing			
index		sheet															

HEADER PINOUT	TYPE	BTB 100 POS RECEPTACLE	HEADER PINOUT	TYPE	BTB 100 POS RECEPTACLE	SHIELD PINOUT	TYPE	BTB 100 POS RECEPTACLE
1	GND	1	35	GND	51	1	GND	4 & 54
2	SIG	2	36	DET	52	2	GND	7 & 57
3	SIG	3	37	SIG	53	3	GND	10 & 60
4	SIG	5	38	SIG	55	4	GND	13 & 63
5	SIG	6	39	SIG	56	5	GND	16 & 66
6	SIG	8	40	SIG	58	6	GND	19 & 69
7	SIG	9	41	SIG	59	7	GND	22 & 72
8	SIG	11	42	SIG	61	8	GND	25 & 75
9	SIG	12	43	SIG	62	9	GND	26 & 76
10	SIG	14	44	SIG	64	10	GND	29 & 79
11	SIG	15	45	SIG	65	11	GND	32 & 82
12	SIG	17	46	SIG	67	12	GND	35 & 85
13	SIG	18	47	SIG	68	13	GND	38 & 88
14	SIG	20	48	SIG	70	14	GND	41 & 91
15	SIG	21	49	SIG	71	15	GND	44 & 94
16	SIG	23	50	SIG	73	16	GND	47 & 97
17	PWR	24	51	PWR	74			
18	SIG	27	52	SIG	77			
19	SIG	28	53	SIG	78			
20	SIG	30	54	SIG	80			
21	SIG	31	55	SIG	81			
22	SIG	33	56	SIG	83			
23	SIG	34	57	SIG	84			
24	SIG	36	58	SIG	86			
25	SIG	37	59	SIG	87			
26	SIG	39	60	SIG	89			
27	SIG	40	61	SIG	90			
28	SIG	42	62	SIG	92			
29	SIG	43	63	SIG	93			
30	SIG	45	64	SIG	95			
31	SIG	46	65	SIG	96			
32	SIG	48	66	SIG	98			
33	SIG	49	67	DET	99			
34	GND	50	68	GND	100			

NOTES:

1 ORDER MATING RECEPTACLES SEPARATELY.

2 RECOMMENDED SCREW TORQUE: 1.0 TO 1.5 MAX in-lbs. (1.2-1.7 cm-kgs).
RECOMMENDED HOLD-DOWN - 2mm SCREWS (95121)
AND HEX NUTS (92869).

3 MATERIAL:

3.1 HEADER ASSY:

PLASTIC HOUSING: HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK - ABOVE PCB
HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK - BELOW PCB

PIN: PHOSPHOR BRONZE

PCB: FR4

3.2 MECHANISM ASSY:

PLASTIC GUIDE: HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK

COVER PLATE: STAINLESS STEEL

EMI CONTACT: PHOSPHOR BRONZE

3.3 .8 BTB RECEPTACLE (73277-101000):

PLASTIC: HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK

CONTACT: BeCu

4 FINISH (PIN)

UNDER PLATING: 0.5um Ni

CONTACT AREA: 0.076 μ m MIN. GOLD

SOLDER TAIL: 2.5um Sn-Pb

2.5um PURE Sn (FOR -***LF)

⑤ DIM "X"

4.25 $\pm$ 0.1	3.5 $\pm$ 0.1	5.0 $\pm$ 0.1
OTHERS	36,67	1,17,34,35,51,68

6 IF LEAD FREE P.N.THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.00MM MINIMUM THICK CIRCUIT BOARD.

7 IF LEAD FREE P/N.THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008

8 LEAD FREE P/N PACKAGING MEETS GS-14-920 SPECIFICATION

9 PRODUCT SPEC:110-263

mat'l. code	surface ISO1302	tolerance ISO1101 ISO406	projection 	product family MCS
ltn ecn nodr date	tolerances unless otherwise specified	angle 	scale 1:1	title CARDBUS DOUBLE DECK ASS'Y SMT TYPE 123
F	0 $\pm$ 2'	0.X $\pm$ 0.3 0.XX $\pm$ 0.13 0.XXX $\pm$ 0.051	MM	dwg no 72306
dr	R.GRAPE	9/9/96	FCI	sheet 9 of 9
engr	D.BRANN	9/9/96		size A4
chr	D.BRANN	9/9/96		type Product Customer Drawing
appd	D.BRANN	9/9/96		
sheet index	revision sheet			