



REV.	DATE	DESCRIPTION
NC	03/23/99	INITIAL RELEASE
A	05/22/07	UPDATE DRAWING FORMAT
B	09/20/07	REVISE BODY PLATING TO NEXCOTE



RECOMMENDED
CABLE STRIPPING DIM'S

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS	DATE	Amphenol Connex								
8						DRAWN	G.R.S.					09/20/07	PART DESCRIPTION N R/A DIRECT SOLDER PLUG (FOR .085”, .086” SEMI RIGID CABLE)			
7						CHECKED										
6						ISSUED			DWG. NO. 172235.DWG							
5						SHEET	1 OF 1						REV. B			
4	BARREL	BRASS	GOLD	1												
3	CONTACT PIN	BRASS	GOLD	1					SCALE NA							
2	INSULATOR	TEFLON	NATURAL	1				C:/172/172235.DWG								
1	BODY	BRASS	NEXCOTE	1									DO NOT SCALE DRAWING			
	DESCRIPTION	MATERIAL	FINISH	QTY								DWG. NO. 172235.DWG				
								REV. B								
																SIZE A