






Copyright FCI.



Cotes	A	B	C	D	E	F	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.21	2.74	1.37	D09S13A4UV00**	D09S13A6UV00**
15	39.14	33.32	25.18	24.54	2.74	1.37	D15S13A4UV00**	D15S13A6UV00**
25	53.03	47.04	39.12	38.25	2.76	1.38	D25S13A4UV00**	D25S13A6UV00**
37	69.32	63.50	55.68	54.71	2.76	1.38	D37S13A4UV00**	D37S13A6UV00**

gold flash 0.76 μ gold

LF FOR LEAD FREE

Technical characteristics:

Shell:steel tin/ZincCr3 plated
Insulators:self-extinguishing thermoplastic ,ULclass94V0
Contacts size 20,phosphor bronze, gold on mating end,bright tin on termination end over nickel on entire contact
Cycles :200 min for plating 4
Cycles :500 min for plating 6
screwlock:brass,tin/ZincCr3 plated
Metal plate for electrical continuity:brass,tin/ZincCr3plated

Electrical characteristics:

max.current rating:5A
Test voltage:1000V
Rated voltage:300V
Contact resistance:≤15mΩ
Shell resistance:≤5mΩ
Insulation resistance:≥5000MΩ

Climatic characteristics:

Operating temperature range:-55°C +125°C

Dimensions:

in accordance with MIL-C-24308
inches are in parenthesis

Part Number & Date Code Printing

FOR ROHS DETAILS REFER DWG.N0:C01-8646-0000

rev	ecn no	dr	date
D	105-0124	JS	2005/07/27
E	106-0074	SK	2006/06/08
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	JOHN SLEEBA	1996/09/25	ANGULAR LINEAR		0.X		±0.1		size A3	Scale 1:1
Eng	GEORGE VJ	1996/09/25			0.XX		±0.1			
Chr	GEORGE VJ	2005/07/27			0.XX* ±1°		0.XXX ±0.1			
Appr	KVSD 2005/07/27		Product family				D-SUB		Spec ref -	
			title SOCKET CONNECT.SUB right angled spill with screwlock,metal bracket				drawing C01-8646-0168		Rev. E	
			catalog no DELTA-D				CUSTOMER		sheet 1 of 1	

REV F - 2006-04-17