

Power cable - SAC-6P-MINMR/ 2,0-547/MINFS - 1416661

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Power cable, 6-position, PVC, yellow, Plug angled 7/8"-16UNF, on Socket straight 7/8"-16UNF, cable length: 2 m

Why buy this product

- ✓ Easy and safe: 100% electrically tested plug-in components
- ✓ High-performance: connectors and cables with a large conductor cross section for power supply

RoHS

Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 222011
GTIN	4055626222011

Technical data

Dimensions

Length of cable	2 m
-----------------	-----

Ambient conditions

Ambient temperature (operation)	-20 °C ... 105 °C (Plug / socket)
Degree of protection	IP68

General

Rated current at 40°C	8 A
Rated voltage	600 V AC
	600 V DC
Number of positions	6
Insulation resistance	≥ 100 MΩ
Coding	A - standard
Status display	No
Protective circuit/component	Unwired

Power cable - SAC-6P-MINMR/ 2,0-547/MINFS - 1416661

Technical data

General

Insertion/withdrawal cycles	100
Torque	10 lb _F -in.
	1.12 Nm

Material

Contact material	CuZn
Contact surface material	AU
Contact carrier material	PVC
Material of grip body	PVC
Material, knurls	Anodized aluminum

Cable

Cable type	ITC/PLTC
Cable abbreviation	547
AWG signal line	18
Conductor cross section signal conductor	6 x AWG 18
Conductor cross section voltage supply	41 x AWG 34
Wire colors	Green 1, white 2, blue 3, gray 4, yellow 5, brown 6
External sheath, color	yellow
External cable diameter	7.29 mm
Outer sheath, material	PVC
Conductor material	Bare Cu litz wires
Nominal voltage, cable	300 V
Flame resistance	UL 1581, FT4
Other resistance	UV resistant (720 h) UL 2556
Ambient temperature (operation)	-30 °C ... 105 °C (cable, flexible installation)


Standards and Regulations

Flame resistance	UL 1581, FT4
Other resistance	UV resistant (720 h) UL 2556

Drawings


Power cable - SAC-6P-MINMR/ 2,0-547/MINFS - 1416661

Dimensional drawing




7/8"-16UNF plug, angled

Circuit diagram




Dimensional drawing



7/8"-16UNF socket, straight


Schematic diagram



Pin assignment, plug, 7/8"-16UNF, 6-pos., view of male side

Contact assignment of 7/8" plugs/sockets

Schematic diagram



Pin assignment, socket, 7/8"-16UNF, 6-pos., view of female side