


6 mm Square Thin Type Double-action SMD Light Touch Switches

Type: **EVQPR/EVQQ0/EVQ3PR**




■ Features

- External dimensions : 6.0 mm×6.0 mm,
Height : 0.9 mm (Without push plate)
0.95 mm (With push plate)
- Wide selection of double action operating variations
With push plate : 1st 0.7 N, 2nd 2.6 N
Without push plate : 1st 1.0 N, 2nd 2.6 N
- Wide selection of double action operating variations

■ Recommended Applications

- Camera function
(Digital still cameras, Camcorders, Mobile phones, etc.)
- Operating switches for menu scrolling and confirmation for portable equipment.

■ Explanation of Part Numbers














■ Specifications

Type	Snap action/Push-on type SPDT		
Push Plate type	With Push Plate		Without Push Plate
Electrical	Rating	10 μ A 2 Vdc to 20 mA 15 Vdc (Resistive load)	
	Contact Resistance	100 m Ω max.	
	Insulation Resistance	50 M Ω min.	
	Dielectric Withstanding Voltage	100 Vac for 1 minute	
	Bouncing	3 ms max. (ON) 20 ms max. (OFF)	
Mechanical	Operating Force	1st : 0.7 N	1st : 1.0 N
		2nd : 2.6 N	2nd : 2.6 N
	Travel	1st: 0.4 mm	2nd: 0.6 mm
Endurance	Operating Life	30000 cycles min.	
Operating Temperature		-20 °C to +70 °C	
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)	
Minimum Quantity/Packing Unit		5000 pcs. Embossed Taping (Reel Pack)	
Quantity/Carton		25000 pcs.	

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.


00 Oct. 2012

■ Dimensions in mm (not to scale)


No. 1			
With Push Plate EVQQ0 EVQPR (Mounting base with Boss) (With ground terminal)		    <div style="border: 1px solid black; padding: 5px; margin-top: 10px;"> Recommended solder thickness $t=0.15\pm 0.03$ </div> <div style="margin-top: 10px;">  </div> <div style="margin-top: 10px;">  </div>	
Part Numbers EVQQ04A10 EVQPR7A10 EVQPR5A10 EVQPR9A10		Ground Terminal Without Without With With	Boss Without With Without With
		Operating Force 1st/0.7 N, 2nd/2.6 N 1st/0.7 N, 2nd/2.6 N 1st/0.7 N, 2nd/2.6 N 1st/0.7 N, 2nd/2.6 N	Height 0.95 mm 0.95 mm 0.95 mm 0.95 mm
No. 2		Without Push Plate EVQPR EVQ3PR (Mounting base with Boss) (With ground terminal)	
   <div style="border: 1px solid black; padding: 5px; margin-top: 10px;"> Recommended solder thickness $t=0.15\pm 0.03$ </div> <div style="margin-top: 10px;">  </div> <div style="margin-top: 10px;">  </div>			
Part Numbers EVQPRBA09 EVQ3PRA09 EVQPRDA09 EVQPRHA09		Ground Terminal Without Without With With	Boss Without With Without With
		Operating Force 1st/1.0 N, 2nd/2.6 N 1st/1.0 N, 2nd/2.6 N 1st/1.0 N, 2nd/2.6 N 1st/1.0 N, 2nd/2.6 N	Height 0.9 mm 0.9 mm 0.9 mm 0.9 mm

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
 Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Recommended Reflow Soldering Conditions




● Embossed Carrier Taping




Unit: mm												
Part No.	Height	A	B	W	F	E	P ₁	P ₂	P ₀	D ₀ Dia.	t ₁	t ₂
EVQPR/Q0/3PR	0.9, 0.95	6.3±0.3	6.3±0.3	12.0±0.3	5.50±0.15	1.75±0.15	8.00±0.15	2.00±0.15	4.00±0.15	1.5 ^{0.1} _{0.0}	0.30±0.05	1.7 ^{0.2} _{0.1}

● Standard Reel Dimensions in mm (not to scale)




Item	A	B	C	D	E
Rate (mm)	φ380.0±2.0	φ80.0±1.0	φ13.0±0.2	φ21.0±0.8	2.0±0.5
Item	W	T	t	r	
Rate (mm)	13.5±1.0	17.5±1.0	1.0 to 3.0	1.0±0.5	

■ Recommended Shape of Test Pole



■ Recommended Operating Conditions



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panasonic](#):

[EVQ-Q0C03K](#) [EVQ-Q0G03K](#) [EVQ-PR3A10](#) [EVQ-PRBA09](#) [EVQ-PRDA09](#) [EVQ-PRHA09](#) [EVQ-Q0A03K](#) [EVQ-Q04A10](#)