


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS				DOC. NO.	SPC-FD05	Effective:	12/21/98	DCP No.	480
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE	
170	A	RELEASED	SAS	07/21/99	JC	2/16/00	DJC	2/24/00	

- SPECIFICATIONS:**
1. INSULATOR: POLYACETAL
 2. JACK BODY: BRASS, NICKEL PLATED
 3. NUT: BRASS, NICKEL PLATED, 2 PIECES
 4. VOLTAGE: 500V
 5. CURRENT: 36A MAX.
 6. TEMPERATURE: -20 °C TO +80 °C
 7. MAXIMUM PANEL THICKNESS: .60 (15.2)
 8. COLOR: BLACK



DISCLAIMER
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

Tolerances Unless Otherwise Specified	DRAWN BY:	DATE:
Fractions ± 1/32	SCOTT SERRITELLA	07/21/99
Decimals	CHECKED BY:	DATE:
.XX ± .01	JOHN COLE	2/16/00
.XXX ± .005	APPROVED BY:	DATE:
	DANIEL CAREY	2/24/00



DRAWING TITLE:			
ø4mm NON-INSULATED BINDING POST, SOLDER TURRET			
SIZE	DWG. NO.	ELECTRONIC FILE	
A	2303	92N4665.DWG	
SCALE:	NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1