

(Längen der Steck- und Anschlußseite gelten für eingepreßte Steckverbinder)
(mating and termination length of contacts apply to pressed in connectors)

yp — A B C K L M N P Q R S T

Referenzebene Tiefe
datum plane depth

Ebene 3 / level 3 :	$11,2^{+0,2}$
---------------------	---------------

Ebene 2 / level 2 : $9,7^{+0,2}$

Ebene 1 / level 1 : $8,2^{+0,2}$

Steckbereich:
length for mating:

Referenzebene Tiefe
datum plane depth

Technical drawing of a rectangular plate with a grid of holes. The plate is 21x2 units (42x4 units). The grid is 21 columns by 4 rows. The holes are 0.6 units in diameter. The plate has a thickness of 0.05 units. The drawing includes dimensions and labels for position, row, and hole diameter.

Position
position — 1

Reihe
row

21x 2 (=42)

4x 2 (=8)

alle Löcher
all holes

$\phi 0,6$

$\phi 0,05$

22



Empfohlener Lochaufbau und
weitere Informationen siehe: DS 17 00 110 0101
recommended configuration of plated through holes
and further information see: DS 17 00 110 0101

			All Dimensions in mm Original Size DIN A 3			Techn. Character.			Nicht tolerierte Maß/Free size tolerances IEC 61076-4-101		
				Dat.	Name	Maßstab/Scale 2 : 1	har-bus HM Messerleiste Typ B-22 110pol., Anschlußlänge 3,7mm <i>har-bus HM male connector type B-22 110pol., termination length 3,7mm</i>				
35965	05.01.10	Hage.	Detail.	30.10.97	Hm						
34337	25.05.07	Hage.	Insp.	30.10.97	Ko						
28489	26.03.01	HL.	Stand.								
24595	05.08.98	HL.	HARTING Electronics GmbH & Co. KG					TB 17 04 110 x201			Blatt/ page /
22833			D-32339 ESPELKAMP								
Mod.	Dat.	Name					Sub.				