


D90FF06 - D90FF08 D90F06 - D90F10

600 V - 1,000 V Rectifiers

2.0 A Forward Current

30 ns - 50 ns Recovery Time



ELECTRICAL CHARACTERISTICS AND MAXIMUM RATINGS

Part Number	Working Reverse Voltage (Vrwm)	Average Rectified Current (Io)		Reverse Current @ Vrwm (Ir)		Forward Voltage (Vf)		1 Cycle Surge Current tp=8.3ms (Ifsm)	Repetitive Surge Current (Ifrm)	Reverse Recovery Time (3) (Trr)	Thermal Impd. θ_{J-C}	Junction Cap. @50VDC @1kHz (Cj)
		55°C(1)	100°C(2)	25°C	100°C	25°C	25°C	25°C	25°C	25°C	25°C	25°C
	Volts	Amps	Amps	μA	μA	Volts	Amps	Amps	Amps	ns	°C / W	pF
D90FF06	600	2.0	1.0	1.0	25	3.0	1.0	30	5	30	0.8	40
D90FF08	800	2.0	1.0	1.0	25	3.5	1.0	30	5	30	0.8	40
D90F06	600	2.0	1.0	1.0	25	2.5	1.0	30	5	50	0.8	40
D90F08	800	2.0	1.0	1.0	25	3.0	1.0	30	5	50	0.8	40
D90F10	1000	2.0	1.0	1.0	25	3.0	1.0	30	5	50	0.8	40

(1) TC=55°C (2)TC=100°C (3)If=0.5A, Ir=1.0A, Irr=0.25A *Op. Temp.= -65°C to +175°C Stg. Temp.= -65°C to +200°C


Plating:

Option 1:

50 μ in gold over 50 μ in nickel.

Option 2:

50 μ in silver over 50 μ in nickel.



Scale: 6 : 1

Dimensions: In. (mm) • All temperatures are ambient unless otherwise noted. • Data subject to change without notice.



VOLTAGE MULTIPLIERS INC.
8711 W. Roosevelt Ave.
Visalia, CA 93291

TEL 559-651-1402
FAX 559-651-0740
www.voltagemultipliers.com

1,000 V - 1,800 V Rectifiers


1.0 A Forward Current

30 ns - 50 ns Recovery Time

D90FF10R

D90FF18R


D90F18R



ELECTRICAL CHARACTERISTICS AND MAXIMUM RATINGS

Part Number	Working Reverse Voltage	Average Rectified Current		Reverse Current @ Vrwm		Forward Voltage		1 Cycle Surge Current tp=8.3ms (Ifsm)	Repetitive Surge Current (Ifrm)	Reverse Recovery Time (3) (Trr)	Thermal Impd. θ_{J-C}	Junction Cap. @50VDC @1kHz (Cj)
	(Vrwm)	(Io)		(Ir)		(Vf)						
	Volts	55°C(1) Amps	100°C(2) Amps	25°C μA	100°C μA	25°C Volts	25°C Amps	25°C Amps	25°C Amps	25°C ns	25°C °C / W	25°C pF
D90FF10R	1000	1.0	0.75	1.0	25	4.0	0.75	20	4	30	0.8	20
D90FF18R	1800	1.0	0.75	1.0	25	4.0	0.50	20	4	30	0.8	20
D90F18R	1800	1.0	0.75	1.0	25	4.0	0.50	20	4	50	0.8	20

(1) TC=55°C (2) TC=100°C (3) If=0.5A, Ir=1.0A, Irr=0.25A *Op. Temp.= -65°C to +175°C Stg. Temp.= -65°C to +200°C



Scale: 6 : 1

Plating:

Option 1:

50μin gold over 50μin nickel.

Option 2:

50μin silver over 50μin nickel.



Dimensions: In. (mm) • All temperatures are ambient unless otherwise noted. • Data subject to change without notice.



VOLTAGE MULTIPLIERS INC.
8711 W. Roosevelt Ave.
Visalia, CA 93291

TEL 559-651-1402
FAX 559-651-0740
www.voltagemultipliers.com