

MBR835, MBR840, MBR845

Preferred Devices

Axial Lead Rectifiers

... employing the Schottky Barrier principle in a large area metal-to-silicon power diode. State-of-the-art geometry features epitaxial construction with oxide passivation and metal overlap contact. Ideally suited for use as rectifiers in low-voltage, high-frequency inverters, free wheeling diodes, and polarity protection diodes.

- High Current Capability
- Low Stored Charge, Majority Carrier Conduction
- Low Power Loss/High Efficiency
- Highly Stable Oxide Passivated Junction
- Guard-Ring for Stress Protection
- Low Forward Voltage
- High Surge Capacity

Mechanical Characteristics:

- Case: Epoxy, Molded
- Weight: 1.1 gram (approximately)
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead and Mounting Surface Temperature for Soldering Purposes: 220°C Max. for 10 Seconds, 1/16" from case
- Shipped in plastic bags, 500 per bag
- Available Tape and Reeled, 1500 per reel, by adding a "RL" suffix to the part number
- Polarity: Cathode indicated by Polarity Band
- ESD Protection: Human Body Model > 4000 V (Class 3)
for Machine Model > 400 V (Class C)

MAXIMUM RATINGS

Rating	Symbol	Max	Unit
Peak Repetitive Reverse Voltage	V_{RRM}		
Working Peak Reverse Voltage	V_{RWM}		
DC Blocking Voltage	V_R		
MBR835		35	
MBR840		40	
MBR845		45	
Average Rectified Forward Current $T_L = 75^\circ\text{C}$ ($\text{P}_{sijL} = 12^\circ\text{C}/\text{W}$, P.C. Board Mounting, see Note 2)	I_O	8.0	A
Non-Repetitive Peak Surge Current (Surge Applied at Rated Load Conditions Halfwave, Single Phase, 60 Hz)	I_{FSM}	140	A
Operating and Storage Junction Temperature Range (Reverse Voltage Applied)	T_J, T_{stg}	-65 to +125	°C
Voltage Rate of Change (Rated V_R)	dv/dt	10	V/ns



ON Semiconductor™


<http://onsemi.com>

SCHOTTKY BARRIER RECTIFIERS 8.0 AMPERES



AXIAL LEAD
CASE 267-05
(DO-201AD)
STYLE 1

MARKING DIAGRAM



MBR8xx = Device Code
xx = 35, 40 or 45

ORDERING INFORMATION

Device	Package	Shipping
MBR835	Axial Lead	500 Units/Bag
MBR835RL	Axial Lead	1500/Tape & Reel
MBR840	Axial Lead	500 Units/Bag
MBR840RL	Axial Lead	1500/Tape & Reel
MBR845	Axial Lead	500 Units/Bag
MBR845RL	Axial Lead	1500/Tape & Reel

Preferred devices are recommended choices for future use and best overall value.

MBR835, MBR840, MBR845

THERMAL CHARACTERISTICS

Characteristic	Symbol	0.9 in x 0.9 in Copper Pad Size	6.75 in x 6.75 in Copper Pad Size	Unit
Thermal Resistance – Junction-to-Lead (See Note 2 – Mounting Data)	$R_{\theta JL}$	13	12	$^{\circ}\text{C/W}$
Thermal Resistance – Junction-to-Ambient (See Note 2 – Mounting Data)	$R_{\theta JA}$	50	40	

ELECTRICAL CHARACTERISTICS ($T_L = 25^{\circ}\text{C}$ unless otherwise noted)

Characteristic	Symbol	Max	Unit
Maximum Instantaneous Forward Voltage (Note 1) ($i_F = 8.0$ Amps, $T_L = 25^{\circ}\text{C}$)	V_F	0.55	V
Maximum Instantaneous Reverse Current @ Rated dc Voltage (Note 1) $T_L = 25^{\circ}\text{C}$ $T_L = 100^{\circ}\text{C}$	i_R	1.0 50	mA

1. Pulse Test: Pulse Width = 300 μs , Duty Cycle = 2.0%.




Figure 1. Typical Forward Voltage




Figure 2. Maximum Forward Voltage




Figure 3. Typical Reverse Current




Figure 4. Typical Capacitance

MBR835, MBR840, MBR845




Figure 5. $R_{\theta JA}$ versus Copper Area




Figure 6. Current Derating - Lead




Figure 7. Forward Power Dissipation

NOTE 2 — MOUNTING DATA

Mounting Method

P.C. Board with 6.75 sq. in. copper surface.






Figure 8. Thermal Response, Junction-to-Ambient

MBR835, MBR840, MBR845

PACKAGE DIMENSIONS

AXIAL LEAD
CASE 267-05
(DO-201AD)
ISSUE G



NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.

DIM	INCHES			MILLIMETERS	
	MIN	MAX		MIN	MAX
A	0.287	0.374		7.30	9.50
B	0.189	0.209		4.80	5.30
D	0.047	0.051		1.20	1.30
K	1.000	---		25.40	---

STYLE 1:
PIN 1. CATHODE (POLARITY BAND)
2. ANODE

PLEASE CONTACT YOUR ON SEMICONDUCTOR
REPRESENTATIVE FOR INFORMATION

ON Semiconductor and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor

P.O. Box 5163, Denver, Colorado 80217 USA

Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada

Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada

Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free

USA/Canada

Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910

Japan Customer Focus Center

Phone: 81-3-5773-3850

ON Semiconductor Website: www.onsemi.com

Order Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local
Sales Representative