







RECOMMENDED P.C.B. LAYOUT

SCALE 3:1



CIRCUIT: SPST

- NOTES:
1. ALL DIMENSIONS IN MM [INCH]
 2. GENERAL TOLERANCE: $X.X = \pm 0.25$
 $X.XX = \pm 0.25$
 3. TERM. NOS. FOR REFERENCE ONLY.
 4. RATINGS: 12VDC, 50mA
 5. CONTACT MATERIAL: SILVER
 6. OPERATING FORCE: 250 ± 50 gf
 7. TRAVEL: 0.25 ± 0.1 mm
 8. CONTACT RESISTANCE: 100 m Ω Max.
 9. DIELECTRIC STRENGTH: 250 V RMS min.
 10. INSULATION RESISTANCE: 100 Mega Ω min.
 11. ELECTRICAL LIFE: $100,000$ CYCLES min.
 12. ▲ DENOTES CRITICAL PARAMETER
 13. 2002/95/EC (ROHS) COMPLIANT



B		17636	ADDED NOTES 12,13	9/13/07	BF	TITLE				E-SWITCH®			
A		11903	RELEASED FOR PRODUCTION	2/5/02	CJB								
REV.		ECN NO.	DESCRIPTION	DATE	CHKD	SCALE				DATE			
						4:1				9/13/07			
						DR				BF			
						DWG				P010110			
						REV				B			

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED