





PART NO.	NO. OF POS.	DIMENSIONS	
		A _{tot}	B±0.1
WH2D-1/MH2D-1LF	2	7.5	2.5
WH3D-1/MH3D-1LF	3	10.0	5.0
WH4D-1/MH4D-1LF	4	12.5	7.5
WH5D-1/MH5D-1LF	5	15.0	10.0
WH6D-1/MH6D-1LF	6	17.5	12.5
WH7D-1/MH7D-1LF	7	20.0	15.0
WH8D-1/MH8D-1LF	8	22.5	17.5 ^{±0.5}
WH9D-1/MH9D-1LF	9	25.0	20.0 ^{±0.5}
WH10D-1/MH10D-1LF	10	27.5±0.3	22.5 ^{±0.5}
WH11D-1/MH11D-1LF	11	30.0±0.3	25.0 ^{±0.5}
WH12D-1/MH12D-1LF	12	32.5±0.3	27.5 ^{±0.5}
WH13D-1/MH13D-1LF	13	35.0±0.3	27.5 ^{±0.5}

TABLE 1



SEE NOTE 3



PCB LAYOUT RECOMMENDED

- NOTES:
1. MATERIAL :
NYLON 66, UL94V-0 RATED.
 2. ORDERING INFORMATION:
SEE TABLE 1
 3. FLASH : 0.2 MAX.
 4. APPEARANCE : 0.3 MAX.
 5. THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO A
MANUFACTURING SOLDER PROCESS (WAVE SOLDER & SMT)

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		A FCI www.fciconnect.com	
ltr	ecn no	dr	date	.X ± .35				projection 	title	product family	code
A	TD4-0027	M W	01/19/04	.XX ± .20							
B	TD5-0219	L S	09/23/05	.XXX ± .10					WIRE HOLDER 2.5MM PITCH	DIPMATE	—
				0° ± 2°							
				dr	MAGIE WU 01/19/04				MM ↔ scale		
				engr	LEIF SHEN 01/19/04						
				chr	PAUL WANG 01/19/04						
									3.1		
				oprd	JOSEPH HSIEH 01/19/04						
sheet	revision	B						A4	JPD22942	sheet	
index	sheet	1									1 of 1