



REV	DOCUMENT	CHANGED BY	CHECK
A	0036603	KRB 07JAN08	RJ



- 1 - SWITCHES ARE CAPABLE OF WITHSTANDING A TEMPERATURE OF 160°F CONTINUOUSLY AT FULL RATED LOAD
- 2 - CIRCUIT DESIGNATION. MICRO SWITCH CATALOG LISTING AND DATE CODE STAMPED ON SIDE OF SWITCH
- 3 - FURNISHED UNASSEMBLED
- 4 - APPLIES ONLY TO " ON" AND "MOMENTARY ON" POSITIONS
- 5 - THE SEALING GROMMET SHALL SEAL ON A SMOOTH WIRE INSULATION OF .068 TO .103 DIAMETERS (14 - 16 GAGE)
- 6 - UNUSED TERMINAL HOLES MAY BE SEALED WITH PLUGS M83723 / 28 -16

DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± 0.040 ONE PLACE .X ± 0.030 TWO PLACE .XX ± 0.015 THREE PLACE .XXX ± 0.005 FOUR PLACE .XXXX ± 0.0005 ANGLES ± 2	DRAWN	KRB	04 DEC 08	Honeywell				
	CHECK	MJS	04 DEC 08					
	THIRD ANGLE PROJECTION 	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH, TOGGLE			
		INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME	REV
		RASTER			C	I	15PA320- TL	A
				SCALE	NTS		SHEET 1 OF 1	