

Products

[Home](#) > [Products](#) > [Industrial Use](#) > NL10276BC30-34D

▼	Products
▶	Monitor Use
▶	Industrial Use
▶	Mobile Use

Products Industrial Use

NL10276BC30-34D

15.0-inch XGA for industrial applications

Screen size	15.0 inch (38cm diagonal)	Interface	LVDS (RGB 8 bits each)
Resolution	1024(H) x 768(V) pixels	Power supply voltage	3.3V
Display area	304.128(H) x 228.096 (V) mm	Power consumption (*3)	10.6W
Drive system	a-Si TFT active- matrix	Operating temperature	-20 °C to +70°C
Display color	16.77M colors	Storage temperature	-20 °C to +80 °C
Pixel arrangement	RGB vertical stripe	Polarizer surface	Antiglare
Pixel pitch	0.297(H) x 0.297(V) mm	Module size	326.5(W) x 253.5(H) x 12.0 max.(D) mm
Luminance	400cd/m ²	Weight	970g
Contrast ratio	600:1	Reverse scan	Yes
Viewing angle (*1)	Up: 80 ° , down: 80 ° , left: 80 ° , right: 80 °	Backlight	White LED (Replaceable)
Response time (*2)	18ms	Recommended inverter	-
Remarks	 		

(*1) Contrast of 10:1 or higher

(*2) Value of Ton+Toff(10% < - > 90%)

(*3) Value does not include power consumption of recommended inverter

All values are typical values (except for the thickness dimension).
All specifications shown on this web site are subject to change without notice.