

AVAILABLE
THROUGH
DISTRIBUTION



BOURNS®

Electrical Characteristics

Standard Resistance Range

.....100 to 1 megohm
(see standard resistance table)
Resistance Tolerance±25% std.
Absolute Minimum Resistance
.....2% max. ($\leq 2K = 30$ ohms)
Contact Resistance Variation ...3% max.
Resolution.....Infinite
Adjustment Angle215° nom.

Environmental Characteristics

Power Rating (100 volts max.)
70°C0.2 watt
Temperature Range-25°C to +100°C
Temperature Coefficient±250ppm/°C
Load Life ..1,000 hours 0.2 watt @ 70°C
(5% ΔTR)

Physical Characteristics

Mechanical Angle.....260° ±20°
Torque (Operating).....4.5 oz-in. max.
Stop Strength6.5 oz-in. min.
TerminalsSolderable pins
MarkingManufacturer's
trademark, resistance code
Standard Packaging300 pcs. per bag
Adjustment ToolH-90
Aqueous cleaning not recommended

How To Order

3306 W - 1 - 103

Model _____
Style _____
Standard Product _____
Resistance Code _____

Standard Resistance Table

Resistance (Ohms)	Resistance Code
100	101
200	201
500	501
1,000	102
2,000	202
5,000	502
10,000	103
20,000	203
25,000	253
50,000	503
100,000	104
200,000	204
250,000	254
500,000	504
1,000,000	105

Popular values listed in boldface. Special resistances available.

SHADED AREA NOT TYPICALLY STOCKED BY DISTRIBUTORS AND NOT RECOMMENDED FOR NEW DESIGNS.


Features

- 6mm Round / Single-Turn / Cermet Industrial / Open Frame
- Cross slot adjustment options
- Horizontal and vertical mounting styles
- Dust resistant/splash resistant covers
- PC board stand-offs and retention feature


■ Front and top adjust styles

3306 - 6mm Round Trimming Potentiometer


Top Adjust Common Dimensions




3306P




3306F




SUGGESTED PWB LAYOUT - STYLE F




Side Adjust Common Dimensions





3306W



3306K



SUGGESTED PWB LAYOUT - STYLES K, P, W



TOLERANCES: ± 0.25 (.010) EXCEPT WHERE NOTED

DIMENSIONS ARE: METRIC (INCHES)