


**FLEX
STACK**

SHROUDED HEADERS & STACKERS

(1.27 mm) .050" PITCH • TML/ZML SERIES



TML/ZML

Mates:

SMS, RSM

SPECIFICATIONS

TML

Insulator Material:

Black Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Au or Sn over

50 μ " (1.27 μ m) Ni

Operating Temp Range:

-55 $^{\circ}$ C to +105 $^{\circ}$ C with Tin;

-55 $^{\circ}$ C to +125 $^{\circ}$ C with Gold

ZML

Insulator Material:

Black Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Au or Sn over

50 μ " (1.27 μ m) Ni

Operating Temp Range:

-55 $^{\circ}$ C to +105 $^{\circ}$ C with Tin;

-55 $^{\circ}$ C to +125 $^{\circ}$ C with Gold

PROCESSING

TML

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0.10 mm) .004" max (05-20)

(0.15 mm) .006" max (32)*

*(.004" stencil solution

may be available; contact

ipg@samtec.com)

ZML

Same as TML except:

SMT Lead Coplanarity:

(0.15 mm) .006" max*

*(.004" stencil solution

may be available; contact

ipg@samtec.com)

ALSO AVAILABLE

Contact Samtec

Other sizes

Other platings

Notes:

For added mechanical stability, Samtec recommends mechanical board spacers be used in applications with gold or selective gold plated connectors. Contact ipg@samtec.com for more information.

Some sizes, styles and options are non-standard, non-returnable.

TML	-	1	NO. PINS PER ROW	-	LEAD STYLE	-	PLATING OPTION	-	D	-	TAIL OPTION	-	OTHER OPTION
-----	---	---	------------------	---	------------	---	----------------	---	---	---	-------------	---	--------------

05, 08,
10, 20, 32
(Standard sizes)

Specify
LEAD
STYLE
from
chart

-F
= Gold flash
on post,
Matte Tin on tail

-L
= 10 μ " (0.25 μ m)
Gold on post,
Matte Tin on tail


-G
= 10 μ " (0.25 μ m)
Gold on post,
Gold flash on tail

(Leave blank for
Through-hole)

-RA
= Right-angle

-SM
= Surface Mount
(For locking clip
add -LC)

-“XXX”
= Polarized
position
(Specify position
of omitted pin)



ZML	-	1	NO. PINS PER ROW	-	LEAD STYLE	-	PLATING OPTION	-	D	-	BODY HEIGHT	-	TAIL OPTION
-----	---	---	------------------	---	------------	---	----------------	---	---	---	-------------	---	-------------

05, 08,
10, 20, 32
(Standard sizes)

Specify
LEAD
STYLE
from
chart

-L
= 10 μ "
(0.25 μ m)
Gold on post,
Matte Tin on tail

-G
= 10 μ "
(0.25 μ m)
Gold on post,
Gold flash on tail

(Leave blank for
Through-hole)

-“XXX”
= -SM Body Height
(Specify board space
“B” in inches from
lead style charts.)

(Leave blank for
Through-hole)

-SM
= Surface
Mount

