





PRODUCT NO.
SEE TABLE



SECTION Y-Y

mat'l. code				surface		tolerance		projection		product family				
				ISO 1302 ✓		ISO 406 ISO 1101				HEADERS				
ltr	ecn no	dr	date	tolerances unless otherwise specified				INCH/MM	title					
A	V71646	SAR	12/15/97	angles linear						scale 1:1	HEADER, SLIM-LINE VERTICAL ASS'Y, 2-WALL			
B	V81270	SAR	8/5/98		.XX±.01/.3									
C	V94352	DAI	11/17/99		.XXX±.005/.13 .XXXX±.0020/.051									
D	M05-0089	ERE	5/20/05	dr	S. ROYER	12/15/97		dwg no	sheet 1 of 2	size				
E	M07-0116	AGS	2/25/07	enrg	L. FYE	12/15/97								
				chr	L. FYE	12/15/97								
				appd	L. FYE	12/15/97								
sheet index		revision sheet		E	E									
				1	2									

PRODUCT NO.

74374 - F ZZ Y LF

F	PLATING NOTE 10
1	30μ / 0.76μm GOLD
5	30μ / 0.76μm GXT

NO. OF PINS ZZ	POSITIONS	DIM B	DIM C
10	2 X 5	.630/16.00	.400/10.16
14	2 X 7	.830/21.80	.600/15.24
26	2 X 13	1.430/35.60	1.200/30.48
34	2 X 17	1.830/46.48	1.600/40.64
40	2 X 20	2.130/54.10	1.900/48.26

Y	DIM D TAIL LENGTH
2	.120/3.05

LEAD FREE OPTION
NOTE 7

NOTES:

- ① PLASTIC MATERIAL: 30% GLASS FILLED, BLACK PCT
FLAME RETARDANT PER UL-94-V0
- ② PIN MATERIAL: PHOS BRONZE.
3. 4 LBS/1.8 KG MIN PIN RETENTION.
- ④ PIN CONTACT SURFACE IS TO BE FREE OF BURRS,
SCRATCHES AND PLASTIC DEBRIS.
5. PACKAGING: ADD 'T' TO THE END OF THE 4-DIGIT DASH NO.
TUBE PACKAGING. [ex 74374-1402T]
6. PART NUMBERS WITH "R" FOLLIWING THE DASH NUMBER
WILL HAVE RETENTIVE TAILS. [ex 74374-1402TR]
TWO PAIR OF PINS LOCATED APPROXIMATELY IN THE CENTER
OF 2X14 AND SMALLER SIZE ARE TO BE KINKED.
TWO PAIR OF PINS LOCATED ON EACH END OF 2X15 AND LARGER
ARE TO HAVE 2 PAIR OF PINS KINKED ON EACH END.
- ⑦ ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
8. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5mm
MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES
IF THEY ARE AVAILABLE.
- ⑨ THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- ⑩ PLATING OPTIONS:
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family HEADERS
ltr	ecn	no	dr	date	tolerances unless otherwise specified	INCH/MM scale 1:1	title
E					angles linear .XX±.01/.3 0°±2° .xxx±.005/.13 .xxxx±.0020/.051		HEADER, SLIM-LINE VERTICAL ASS'Y, 2-WALL
			dr	S. ROYER	12/15/97		dwg no
			enrg	L. FYE	12/15/97		sheet2 of 2 size
			chr	L. FYE	12/15/97		74374 A3
			appd	L. FYE	12/15/97		type Product Customer Drawing
sheet index	revision sheet						

form: A3