

LOC —	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	REVISED PER ECR-10-023099	16NOV10	HMR	DD




- 1

 HIGH CONDUCTIVITY COPPER ALLOY, 0.30[.012]THK.
- 2

 WIRE RANGE: 3-6mm² [12-10 AWG].
- 3


 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 4

 PRE-TIN PLATED.



SECTION A-A
SCALE 10:1

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R BROWN 16OCT2008		FINISH		MATERIAL		2058931-1	
		CHK D FLEMING 16OCT2008		Tyco Electronics Corporation Harrisburg, PA 17105-3608		PART NUMBER			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD —		NAME		SOCKET, UNIVERSAL MATE-N-LOK(TM) II	
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC —		APPLICATION SPEC —		RESTRICTED TO	
MATERIAL —		FINISH —		WEIGHT —		SIZE A2		CAGE CODE 00779	
						DRAWING NO C-2058931			
						SCALE 4:1		SHEET 1 of 1	
						REV A			