

Aluminum Capacitors Miniature, Axial Lead, High Reliability



Fig.1 Component outline

FEATURES

- Wide temperature range
- Foil tantalum replacement
- Unique Teflon end seal for long life
- High vibration capability
- Life test 2000 hours at + 125 °C



QUICK REFERENCE DATA	
DESCRIPTION	VALUE
Nominal case size Ø D x L in mm	0.276" x 0.945" [7.0 x 24.0] to 0.374" x 2.677" [9.5 x 68.0]
Operating temperature	- 55 °C to + 125 °C
Rated Capacitance range, C _R	2.2 µF to 2700 µF
Tolerance on C _R	+ 10 %, + 50 %; - 10 %, + 75 %
Rated voltage range, U _R	5 WVDC to 250 WVDC
Termination	2 axial leads
Life validation test at 125 °C	2000 hours: Δ CAP ≤ 15 % from initial measurement Δ ESR ≤ 1.3 x initial specified limit Δ DCL ≤ initial specified limit
Shelf life at 125 °C	500 hours: Δ CAP ≤ 10 % from initial measurement Δ ESR ≤ 1.5 x initial specified limit Δ DCL ≤ 2 x the initial specified limit
DC leakage current	0 WVDC to 75 WVDC $I = 0.15 \sqrt{CV}$ I in µA, C in µF, V in Volts 100 WVDC to 250 WVDC $I = 0.15 \sqrt{CV} + 5$

RIPPLE CURRENT MULTIPLIERS				
TEMPERATURE				
Ambient Temperature		Multipliers		
+ 125 °C		1.0		
+ 85 °C		2.0		
+ 75 °C or less		2.4		
FREQUENCY (Hz)				
WVDC	50 - 60	100 - 120	300 - 400	> 1000
0 - 30	0.85	1.0	1.04	1.08
31 - 250	0.80	1.0	1.30	1.40

DIMENSIONS in inches [millimeters]				
CASE CODE	BARE CASE		WITH OUTER INSULATION	
	DIAMETER	LENGTH	DIAMETER	LENGTH (Max.)
KD	0.281 ± 0.016 [7.14 ± 0.40]	0.937 ± 0.031 [23.81 ± 0.79]	0.297 ± 0.031 [7.54 ± 0.79]	1.00 [25.40]
DD	0.375 ± 0.016 [9.53 ± 0.40]	0.937 ± 0.031 [23.81 ± 0.79]	0.391 ± 0.031 [9.92 ± 0.79]	1.00 [25.40]
DE	0.375 ± 0.016 [9.53 ± 0.40]	1.125 ± 0.031 [28.58 ± 0.79]	0.391 ± 0.031 [9.92 ± 0.79]	1.187 [30.16]
DG	0.375 ± 0.016 [9.53 ± 0.40]	1.375 ± 0.031 [34.93 ± 0.79]	0.391 ± 0.031 [9.92 ± 0.79]	1.437 [36.51]
DJ	0.375 ± 0.016 [9.53 ± 0.40]	1.625 ± 0.031 [41.28 ± 0.79]	0.391 ± 0.031 [9.92 ± 0.79]	1.687 [42.86]
DL	0.375 ± 0.016 [9.53 ± 0.40]	2.187 ± 0.031 [55.56 ± 0.79]	0.391 ± 0.031 [9.92 ± 0.79]	2.249 [57.12]
DX	0.375 ± 0.016 [9.53 ± 0.40]	2.687 ± 0.031 [68.26 ± 0.79]	0.391 ± 0.031 [9.92 ± 0.79]	2.749 [69.82]

ELECTRICAL DATA

SYMBOL	DESCRIPTION
μF	rated capacitance
$\pm \%$	F = - 10, + 50 %
DC	voltage rating at 85 °C
KD	case code
4	case style

ORDERING EXAMPLE*

Electrolytic capacitor 600D series

600D 227F 005 KD 4

* Note: For lead (Pb)-free / RoHS compliant products add suffix "E3" to part number

Example: 600D227F005KD4E3

ELECTRICAL DATA AND ORDERING INFORMATION

CAPACITANCE (μF)	PART NUMBER	NOMINAL CASE SIZE D x L	Max. ESR at + 25 °C 120 Hz	Max. RIPPLE at + 125 °C 120 Hz
5 WVDC at + 85 °C . . . 3 WVDC at + 125 °C				
220	600D227F005KD4	0.281 x 0.937 [7.14 x 23.8]	1.75	0.127
470	600D477F005DD4	0.375 x 0.937 [9.53 x 23.8]	0.813	0.221
680	600D687F005DE4	0.375 x 1.126 [9.53 x 28.6]	0.564	0.286
1000	600D108F005DG4	0.375 x 1.378 [9.53 x 35.0]	0.388	0.377
1200	600D128F005DJ4	0.375 x 1.626 [9.53 x 41.3]	0.32	0.477
1800	600D188F005DL4	0.375 x 2.185 [9.53 x 55.5]	0.21	0.631
2700	600D278F005DX4	0.375 x 2.685 [9.53 x 68.2]	0.14	0.851
7 WVDC at + 85 °C . . . 5 WVDC at + 125 °C				
180	600D187F007KD4	0.281 x 0.937 [7.14 x 23.8]	2.121	0.115
390	600D397F007DD4	0.375 x 0.937 [9.53 x 23.8]	0.972	0.202
470	600D477F007DE4	0.375 x 1.126 [9.53 x 28.6]	0.813	0.238
680	600D687F007DG4	0.375 x 1.378 [9.53 x 35.0]	0.564	0.312
1000	600D108F007DJ4	0.375 x 1.626 [9.53 x 41.3]	0.388	0.406
1500	600D158F007DL4	0.375 x 2.185 [9.53 x 55.5]	0.26	0.567
2200	600D228F007DX4	0.375 x 2.685 [9.53 x 68.2]	0.175	0.761
10 WVDC at + 85 °C . . . 7 WVDC at + 125 °C				
120	600D127F010KD4	0.281 x 0.937 [7.14 x 23.8]	3.18	0.094
330	600D337F010DD4	0.375 x 0.937 [9.53 x 23.8]	1.16	0.185
390	600D397F010DE4	0.375 x 1.126 [9.53 x 28.6]	0.972	0.218
560	600D567F010DG4	0.375 x 1.378 [9.53 x 35.0]	0.673	0.286
820	600D827F010DJ4	0.375 x 1.626 [9.53 x 41.3]	0.46	0.373
1200	600D128F010DL4	0.375 x 2.185 [9.53 x 55.5]	0.318	0.513
1500	600D158F010DX4	0.375 x 2.685 [9.53 x 68.2]	0.23	0.664
15 WVDC at + 85 °C . . . 10 WVDC at + 125 °C				
100	600D107F015KD4	0.281 x 0.937 [7.14 x 23.8]	3.88	0.085
220	600D227F015DD4	0.375 x 0.937 [9.53 x 23.8]	1.75	0.15
330	600D337F015DE4	0.375 x 1.126 [9.53 x 28.6]	1.16	0.199
470	600D477F015DG4	0.375 x 1.378 [9.53 x 35.0]	0.813	0.26
560	600D567F015DJ4	0.375 x 1.626 [9.53 x 41.3]	0.686	0.305
820	600D827F015DL4	0.375 x 2.185 [9.53 x 55.5]	0.46	0.426
1200	600D128F015DX4	0.375 x 2.685 [9.53 x 68.2]	0.32	0.563

**ELECTRICAL DATA AND ORDERING INFORMATION**

CAPACITANCE (μ F)	PART NUMBER	NOMINAL CASE SIZE D x L	Max. ESR at + 25 °C 120 Hz	Max. RIPPLE at + 125 °C 120 Hz
20 WVDC at + 85 °C . . . 15 WVDC at + 125 °C				
68	600D686F020KD4	0.281 x 0.937 [7.14 x 23.8]	4.274	0.081
150	600D157F020DD4	0.375 x 0.937 [9.53 x 23.8]	1.962	0.142
220	600D226F020DE4	0.375 x 1.126 [9.53 x 28.6]	1.325	0.186
330	600D337F020DG4	0.375 x 1.378 [9.53 x 35.0]	0.883	0.25
390	600D397F020DJ4	0.375 x 1.626 [9.53 x 41.3]	0.257	0.299
680	600D687F020DL4	0.375 x 2.185 [9.53 x 55.5]	0.564	0.385
820	600D827F020DX4	0.375 x 2.685 [9.53 x 68.2]	0.36	0.53
30 WVDC at + 85 °C . . . 20 WVDC at + 125 °C				
47	600D476F030KD4	0.281 x 0.937 [7.14 x 23.8]	3.06	0.096
100	600D107F030DD4	0.375 x 0.937 [9.53 x 23.8]	1.50	0.162
150	600D157F030DE4	0.375 x 1.126 [9.53 x 28.6]	1.00	0.215
220	600D227F030DG4	0.375 x 1.378 [9.53 x 35.0]	0.675	0.285
270	600D277F030DJ4	0.375 x 1.626 [9.53 x 41.3]	0.56	0.338
390	600D397F030DL4	0.375 x 2.185 [9.53 x 55.5]	0.375	0.472
560	600D567F030DX4	0.375 x 2.685 [9.53 x 68.2]	0.264	0.62
40 WVDC at + 85 °C . . . 30 WVDC at + 125 °C				
33	600D336F040KD4	0.281 x 0.937 [7.14 x 23.8]	4.50	0.079
82	600D826F040DD4	0.375 x 0.937 [9.53 x 23.8]	1.824	0.147
100	600D107F040DE4	0.375 x 1.126 [9.53 x 28.6]	1.50	0.175
150	600D157F040DG4	0.375 x 1.378 [9.53 x 35.0]	1.00	0.234
180	600D187F040DJ4	0.375 x 1.626 [9.53 x 41.3]	0.844	0.275
270	600D277F040DL4	0.375 x 2.185 [9.53 x 55.5]	0.54	0.394
390	600D397F040DX4	0.375 x 2.685 [9.53 x 68.2]	0.397	0.505
50 WVDC at + 85 °C . . . 40 WVDC at + 125 °C				
22	600D226F050KD4	0.281 x 0.937 [7.14 x 23.8]	6.75	0.065
56	600D566F050DD4	0.375 x 0.937 [9.53 x 23.8]	2.65	0.122
68	600D686F050DE4	0.375 x 1.126 [9.53 x 28.6]	2.17	0.146
100.0*	600D107F050DG4	0.375 x 1.378 [9.53 x 35.0]	1.50	0.192
150	600D157F050DJ4	0.375 x 1.626 [9.53 x 41.3]	1.00	0.253
180	600D187F050DL4	0.375 x 2.185 [9.53 x 55.5]	0.844	0.315
270	600D277F050DX4	0.375 x 2.685 [9.53 x 68.2]	0.54	0.433
60 WVDC at + 85 °C . . . 50 WVDC at + 125 °C				
15	600D156F060KD4	0.281 x 0.937 [7.14 x 23.8]	9.65	0.055
39	600D396F060DD4	0.375 x 0.937 [9.53 x 23.8]	3.85	0.102
47	600D476F060DE4	0.375 x 1.126 [9.53 x 28.6]	3.06	0.123
82	600D826F060DG4	0.375 x 1.378 [9.53 x 35.0]	1.82	0.174
100	600D107F060DJ4	0.375 x 1.626 [9.53 x 41.3]	1.50	0.207
150	600D157F060DL4	0.375 x 2.185 [9.53 x 55.5]	1.00	0.29
220	600D227F060DX4	0.375 x 2.685 [9.53 x 68.2]	0.675	0.388

ELECTRICAL DATA AND ORDERING INFORMATION

CAPACITANCE (μ F)	PART NUMBER	NOMINAL CASE SIZE D x L	Max. ESR at + 25 °C 120 Hz	Max. RIPPLE at + 125 °C 120 Hz
75 WVDC at + 85 °C . . . 60 WVDC at + 125 °C				
12.0*	600D126F075KD4	0.281 x 0.937 [7.14 x 23.8]	12.3	0.048
27	600D276F075DD4	0.375 x 0.937 [9.53 x 23.8]	5.625	0.084
39	600D396F075DE4	0.375 x 1.126 [9.53 x 28.6]	3.857	0.11
56	600D566F075DG4	0.375 x 1.378 [9.53 x 35.0]	2.64	0.144
82	600D826F075DJ4	0.375 x 1.626 [9.53 x 41.3]	1.82	0.187
120	600D127F075DL4	0.375 x 2.185 [9.53 x 55.5]	1.227	0.261
150	600D157F075DX4	0.375 x 2.685 [9.53 x 68.2]	1.00	0.399
100 WVDC at + 85 °C . . . 75 WVDC at + 125 °C				
6.8	600D685F100KD4	0.281 x 0.937 [7.14 x 23.8]	22.5	0.036
22	600D226F100DD4	0.375 x 0.937 [9.53 x 23.8]	6.75	0.077
27	600D276F100DE4	0.375 x 1.126 [9.53 x 28.6]	5.625	0.091
39	600D396F100DG4	0.375 x 1.378 [9.53 x 35.0]	3.857	0.12
56	600D566F100DJ4	0.375 x 1.626 [9.53 x 41.3]	2.64	0.156
82	600D826F100DL4	0.375 x 2.185 [9.53 x 55.5]	1.824	0.215
120	600D127F100DX4	0.375 x 2.685 [9.53 x 68.2]	1.27	0.91
150 WVDC at + 85 °C . . . 100 WVDC at + 125 °C				
3.3	600D335F150KD4	0.281 x 0.937 [7.14 x 23.8]	38.30	0.028
6.8	600D685F150DD4	0.375 x 0.937 [9.53 x 23.8]	19.16	0.046
12.0*	600D126F150DE4	0.375 x 1.126 [9.53 x 28.6]	10.5	0.066
18	600D186F150DG4	0.375 x 1.378 [9.53 x 35.0]	6.85	0.09
22.0*	600D226F150DJ4	0.375 x 1.626 [9.53 x 41.3]	5.75	0.106
33.0*	600D336F150DL4	0.375 x 2.185 [9.53 x 55.5]	3.83	0.148
47	600D476F150DX4	0.375 x 2.685 [9.53 x 68.2]	2.61	0.197
200 WVDC at + 85 °C . . . 150 WVDC at + 125 °C				
3.3	600D335F200KD4	0.281 x 0.937 [7.14 x 23.8]	38.30	0.028
6.8	600D685F200DD4	0.375 x 0.937 [9.53 x 23.8]	19.16	0.046
8.2	600D825F200DE4	0.375 x 1.126 [9.53 x 28.6]	15.50	0.055
12	600D126F200DG4	0.375 x 1.378 [9.53 x 35.0]	10.50	0.073
18	600D186F200DJ4	0.375 x 1.626 [9.53 x 41.3]	6.78	0.098
27.0	600D276F200DL4	0.375 x 2.185 [9.53 x 55.5]	4.790	0.132
33.0	600D336F200DX4	0.375 x 2.685 [9.53 x 68.2]	3.830	0.162
250 WVDC at + 85 °C . . . 200 WVDC at + 125 °C				
2.2	600D225F250KD4	0.281 x 0.937 [7.14 x 23.8]	57.50	0.023
5.6*	600D565F250DD4	0.375 x 0.937 [9.53 x 23.8]	23.10	0.042
6.8*	600D685F250DE4	0.375 x 1.126 [9.53 x 28.6]	19.16	0.05
10.0*	600D106F250DG4	0.375 x 1.378 [9.53 x 35.0]	12.70	0.066
15	600D156F250DJ4	0.375 x 1.626 [9.53 x 41.3]	8.23	0.088
22.0*	600D226F250DL4	0.375 x 2.185 [9.53 x 55.5]	5.75	0.121
27.0*	600D276F250DX4	0.375 x 2.685 [9.53 x 68.2]	4.79	0.146

Note

* These values are normally stocked. Other ratings available as special order.



Aluminum Capacitors
Miniature, Axial Lead, High Reliability

600D
Vishay Sprague

ELECTRICAL DATA AND ORDERING INFORMATION - original ratings**

CAPACITANCE (μ F)	CASE CODE	PART NUMBER
7 WVDC at + 85 °C . . . 5 WVDC at + 125 °C		
220	DD	600D227G007DD4
270	DE	600D277G007DE4
390	DG	600D397G007DG4
560	DJ	600D567G007DJ4
820	DL	600D827G007DL4
1000	DX	600D108G007DX4
10 WVDC at + 85 °C . . . 7 WVDC at + 125 °C		
100	KD	600D107G010KD4
180	DD	600D187G010DD4
220.0*	DE	600D227G010DE4
330	DG	600D337G010DG4
470	DJ	600D477G010DJ4
680	DL	600D687G010DL4
820	DX	600D827G010DX4
15 WVDC at + 85 °C . . . 10 WVDC at + 125 °C		
68	KD	600D686G015KD4
82	KD	600D826G015KD4
150	DD	600D157G015DD4
180	DE	600D187G015DE4
270	DG	600D277G015DG4
390	DJ	600D397G015DJ4
560	DL	600D567G015DL4
680	DX	600D687G015DX4
20 WVDC at + 85 °C . . . 15 WVDC at + 125 °C		
68	KD	600D686G020KD4
100.0*	DD	600D107G020DD4
220	DG	600D227G020DG4
30 WVDC at + 85 °C . . . 20 WVDC at + 125 °C		
33	KD	600D336G030KD4
47	KD	600D476G030KD4
82.0*	DD	600D826G030DD4
100	DE	600D107G030DE4
120	DG	600D127G030DG4
150.0*	DG	600D157G030DG4
220	DJ	600D227G030DJ4
330	DL	600D337G030DL4
390	DX	600D397G030DX4
40 WVDC at + 85 °C . . . 30 WVDC at + 125 °C		
50	DD	600D506G040DD4
70	DE	600D706G040DE4
100.0*	DG	600D107G040DG4
140	DJ	600D147G040DJ4
210.0*	DL	600D217G040DL4
50 WVDC at + 85 °C . . . 40 WVDC at + 125 °C		
22.0*	KD	600D226G050KD4
33	DD	600D336G050DD4
47.0*	DE	600D476G050DE4
56	DG	600D566G050DG4
68	DG	600D686G050DG4
100.0*	DJ	600D107G050DJ4
150.0*	DL	600D157G050DL4
180.0*	DX	600D187G050DX4

ELECTRICAL DATA AND ORDERING INFORMATION - original ratings**

CAPACITANCE (μ F)	CASE CODE	PART NUMBER
60 WVDC at + 85 °C . . . 50 WVDC at + 125 °C		
17.0*	KD	600D176G060KD4
80.0*	DJ	600D806G060DJ4
75 WVDC at + 85 °C . . . 60 WVDC at + 125 °C		
12.0*	KD	600D126F075KD4
22.0*	DD	600D226F075DD4
33	DE	600D336F075DE4
47.0*	DG	600D476F075DG4
68.0*	DJ	600D686F075DJ4
100	DL	600D107F075DL4
120.0*	DX	600D127F075DX4
100 WVDC at + 85 °C . . . 75 WVDC at + 125 °C		
8.2	KD	600D825F100KD4
12	DD	600D126F100DD4
15	DE	600D156F100DE4
22	DG	600D226F100DG4
33	DJ	600D336F100DJ4
47.0*	DL	600D476F100DL4
68	DX	600D686F100DX4
150 WVDC at + 85 °C . . . 100 WVDC at + 125 °C		
4.7*	KD	600D475F150KD4
5.6	KD	600D565F150KD4
8.2*	DD	600D825F150DD4
12.0*	DE	600D126F150DE4
18	DG	600D186F150DG4
22.0*	DJ	600D226F150DJ4
33.0*	DL	600D336F150DL4
56.0*	DX	600D566F150DX4
200 WVDC at + 85 °C . . . 150 WVDC at + 125 °C		
3.3	KD	—
3.9	KD	—
5.6	DD	—
8	DE	600D805F200DE4
8.2	DE	—
12	DG	—
15	DJ	—
27	DL	—
39.0*	DX	600D396F200DX4
250 WVDC at + 85 °C . . . 200 WVDC at + 125 °C		
2.2	KD	—
3.3	KD	600D335F250KD4
5.6*	DD	600D565F250DD4
6.8*	DE	600D685F250DE4
10	DG	600D106F250DG4
12.0*	DJ	600D126F250DJ4
22.0*	DL	600D226F250DL4
27.0*	DX	600D276F250DX4

Note

* These values are normally stocked. Other ratings are available on special request.

** Type 600D Original Ratings are recommended for replacement applications only.



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[600D107G050DJ5](#) [600D226G050KD5](#) [600D276F250DX5](#) [600D475F150KD5](#) [600D805F200DE5](#) [600D336F075DE5](#)
[600D107G075DL5](#) [600D107F075DL5](#) [600D567F030DX5](#) [600D106F250DG4](#) [600D107F040DE4](#) [600D107F050DG4](#)
[600D107F060DJ4](#) [600D107G010KD4](#) [600D107G040DG4](#) [600D107G050DJ4](#) [600D126F075KD4](#)
[600D126F200DG4](#) [600D126F250DJ4](#) [600D127F100DX4](#) [600D127G060DL4](#) [600D157F030DE4](#) [600D157F050DJ4](#)
[600D157F075DX4](#) [600D157G030DG4](#) [600D157G050DL4](#) [600D158F010DX4](#) [600D217G040DL4](#) [600D226F075DD4](#)
[600D226F100DD4](#) [600D226F100DG4](#) [600D226F150DJ4](#) [600D226F250DL4](#) [600D226G050KD4](#) [600D227F060DX4](#)
[600D227G020DG4](#) [600D256G060DD4](#) [600D276F250DX4](#) [600D277F050DX4](#) [600D306G040KD4](#)
[600D335F250KD4](#) [600D336F150DL4](#) [600D396F200DX4](#) [600D397F030DL4](#) [600D397F040DX4](#) [600D405F200KD4](#)
[600D476F075DG4](#) [600D476F100DL4](#) [600D476G050DE4](#) [600D565F250DD4](#) [600D566F075DG4](#) [600D607G020DX4](#)
[600D685F250DE4](#) [600D805F200DE4](#) [600D826F060DG4](#) [600D827F020DX4](#) [600D506G040DD4](#)
[600D476F075DG5](#) [600D336F075DE4](#) [600D826G030DD4](#) [600D825F150DD4](#) [600D406G060DE4](#) [600D631](#)
[600D739](#) [600D127F075DX4](#) [600D187G050DX4](#) [600D176F200DJ5](#) [600D176F200DJ4](#) [600D287G040DX4](#)
[600D167G060DX4](#) [600D227G007DD4](#) [600D606G060DG4](#) [600D405F200KD5](#) [600D336G050DD4](#) [600D157F060DL4](#)
[600D176G060KD4](#) [600D686G050DG4](#) [600D567G015DL4](#) [600D475F150KD4](#) [600D566F150DX4](#)
[600D157G050DL5](#) [600D806G060DJ4](#) [600D107F075DL4](#) [600D147G040DJ4](#) [600D227G030DJ4](#) [600D126F100DD4](#)
[600D227G010DE4](#) [600D806G060DJ5](#)