


## ENERGIZER A95

D




### Industry Standard Dimensions



|                         |                                                                              |
|-------------------------|------------------------------------------------------------------------------|
| <b>Classification:</b>  | Alkaline                                                                     |
| <b>Chemical System:</b> | Zinc-Manganese Dioxide (Zn/MnO <sub>2</sub> )<br>No added mercury or cadmium |
| <b>Designation:</b>     | ANSI-13A, IEC-LR20                                                           |
| <b>Nominal Voltage:</b> | 1.5 volts                                                                    |
| <b>Operating Temp:</b>  | -18°C to 55°C (0°F to 130°F)                                                 |
| <b>Typical Weight:</b>  | 144.0 grams (5.1 oz.)                                                        |
| <b>Typical Volume:</b>  | 56.0 cubic centimeters (3.4 cubic inch)                                      |
| <b>Jacket:</b>          | Plastic Label                                                                |
| <b>Shelf Life:</b>      | 7 years at 21°C                                                              |
| <b>Terminal:</b>        | Flat Contact                                                                 |

### Performance Comparison

A95 vs. Typical Carbon Zinc (D) at 21°C



Industry Standard Testing Protocol

### Device Selection Guide:

Portable Stereo



Toy




Lighting



Radio



### Battery Selection Indicator



### Important Notice

This data sheet contains typical information specific to products manufactured at the time of its publication.  
©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.