





FEMALE THREADS: FOR USE WITH MICRO-D'S WITH JACKSCREWS

MALE THREADS: FOR USE WITH MICRO-D'S WITH JACKPOSTS

HOW TO ORDER

Series- Basic Part Number	Shell Plating *	Shell Size (Table I)	Jackscrew Option	Attachment Type	Attach. Length	Dash No. (Table II)
500-017	C – Black Anodize	09	MB – Fillister (slot) head	F – Wire Rope, Nylon Jacket	In One Inch Incre- ments	01
	E – Chem. Film	15	MH – Allen (hex) head			02
	J – Gold Iridite Over	21	F –Female threads	H – Wire Rope, Teflon Jacket		03
	Cadmium Over	25				04
	Electroless Nickel	31		N – No Attachment		05
	M – Electroless Nickel	37		R – Wire Rope, PVC Jacket		06
	NF– Cadmium, Olive Drab Over	51				
	Electroless Nickel	100		T – Wire Rope, No Jacket		
Z 2– Gold						
Sample Part Number:						
500-017	M	31	MB	F	6	01
* SEE PAGE C-4 FOR COMPLETE INFORMATION						

* SEE PAGE C-4 FOR COMPLETE INFORMATION

Metric dimensions (mm) are indicated in parentheses.

500-017
Micro-D Metal Protective Cover



MIL-DTL-83513
Micro-D

TABLE I: DIMENSIONS

SHELL SIZE	A	B	C	D Thread	E Max	F Max
09	.775 (19.7)	.36 (9.1)	.565 (14.4)	2-56 UNC	.453 (11.5)	.930 (23.6)
15	.925 (23.5)	.36 (9.1)	.715 (18.2)	2-56 UNC	.453 (11.5)	1.080 (27.4)
21	1.075 (27.3)	.36 (9.1)	.865 (22.0)	2-56 UNC	.453 (11.5)	1.230 (31.2)
25	1.175 (29.8)	.36 (9.1)	.965 (24.5)	2-56 UNC	.453 (11.5)	1.330 (33.8)
31	1.325 (33.7)	.36 (9.1)	1.115 (28.3)	2-56 UNC	.453 (11.5)	1.480 (37.6)
37	1.475 (37.5)	.36 (9.1)	1.265 (32.1)	2-56 UNC	.453 (11.5)	1.630 (41.4)
51	1.425 (36.2)	.40 (10.2)	1.215 (30.9)	2-56 UNC	.496 (12.6)	1.580 (40.1)
100	2.160 (54.9)	.45 (11.4)	1.800 (45.7)	4-40 UNC	.539 (13.7)	2.315 (58.8)

TABLE II: FASTENER

Dash No.	G Dia
01	.140 (3.6)
02	.182 (4.6)
03	.191 (4.9)
04	.197 (5.0)
05	.167 (4.2)
06	.125 (3.2)

**Metric dimensions (mm) are
indicated in parentheses.**