






LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
IR	—		N2	ECR-11-025628	20DEC2011	PS—

- NOTES:
1. TOLERANCES UNLESS OTHERWISE SPECIFIED:±0,15
 2. FOR APPLICATION INFORMATION SEE TE SPEC. 114-19019.
 3. FOR PERFORMANCE REQUIREMENTS SEE TE SPEC. 108-19064



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P.BEIJNON	19JUN90	TE Connectivity			
		CHK C.A.STERKEN	—	NAME			
		APVD L.V.SOEST	—	MODULAR JACK 8 POS. TOP ENTRY WITH PANEL STOPS PRINTED CIRCUIT BOARD			
		PRODUCT SPEC		SIZE		DRAWING NO	
		APPLICATION SPEC		CAGE CODE		RESTRICTED TO	
		—		A2		00779	
		WEIGHT		C=216566		—	
		CUSTOMER DRAWING		SCALE		SHEET	
				NTS		1 OF 2	
						REV	
						N2	

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
IR	-					
		-		SEE SHEET 1	-	-



PRINTED CIRCUIT BOARD LAYOUT
[VIEW SHOWN IS CIRCUIT (NONCOMPONENT) SIDE OF BOARD.]
TOLERANCES UNLESS OTHERWISE SPECIFIED:±0,05
PRINTED CIRCUIT BOARD THICKNESS: 1,6 mm NOMINAL.

OBSOLETE	180pcs. IN A TRAY 6 TRAYS IN A BOX	8 POSITIONS/ 8 CONTACTS.	<u>IN CONTACT AREA:</u> 1,2µm MIN.SEL.GOLD OVER 1,2µm MIN.NICKEL	HOUSING: <u>PBT,UL 94-HB</u> COLOR: BLACK CONTACTS: PHOSPHOR BRONZE	216566-4
	600pcs. ON A 60cm. DIA. REEL.			HOUSING: <u>PBT,UL 94V-0</u> COLOR: BLACK CONTACTS: PHOSPHOR BRONZE	216566-2
				HOUSING: <u>PBT,UL 94-HB</u> COLOR: BLACK CONTACTS: PHOSPHOR BRONZE	216566-1
				PACKAGING	REMARKS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P.BEIJNON	19JUN90	 TE Connectivity			
DIMENSIONS: mm		CHK C.A.STERKEN	—				
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —	APVD L.V.SOFST	—	NAME MODULAR JACK 8 POS. TOP ENTRY WITH PANEL STOPS PRINTED CIRCUIT BOARD			
		PRODUCT SPEC —					
		APPLICATION SPEC —					
		SIZE	CAGE CODE				
		DRAWING NO					
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT —	A2	00779	C=216566	RESTRICTED TO —	
CUSTOMER DRAWING					SCALE NTS	SHEET 2 of 2	REV N2