


# AD6010(7) SERIES



## External Dimensions



Frame: Plastic(UL:94V-0)  
 Impeller: Plastic(UL:94V-0)  
 Lead wire: UL1007AWG26


## Specifications(Nominal)

\*: Noise is measured at the distance of one (1) meter from the axis of intake.

Bearing type: ◎=Ball ☆=Sleeve ○=1B1S ●=Hypro bearing

Frame size (mm)	Model No.	Bearing	Rated			Rated Speed (rpm)	Maximum AirFlow		Maximum Pressure		*Noise Level (dB/A)	Weight (g)
		System Type	Voltage (VDC)	Current (A)	Power (W)		(CMM)	(CFM)	(InAq)	(mmAq)		
60x60x10	AD0605LB-G70(T)	◎ ☆ ○ ●	5	0.11	0.55	3500	0.276	9.756	0.059	1.510	23.0	23.0
	AD0605MB-G70(T)	◎ ☆ ○ ●	5	0.13	0.65	4200	0.341	12.000	0.090	2.286	28.0	
	AD0612LB-G70(T)	◎ ☆ ○ ●	12	0.09	1.08	3500	0.276	9.756	0.059	1.510	23.0	
	AD0612MB-G70(T)	◎ ☆ ○ ●	12	0.11	1.32	4200	0.341	12.000	0.090	2.286	28.0	
	AD0612HB-G70(T)	◎ ☆ ○ ●	12	0.12	1.44	4900	0.419	14.820	0.118	2.997	35.0	

Specifications subject to change without notice.



\*Motor protective circuit and third lead wire functions

0	1	2	3	4	6	7	8	9	A	B
✓						✓				

\*Safety approvals

✓	✓		✓	✓

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADDA:](#)

[AD0605HB-G70\(T\)-LF](#)