





SPC
TECHNOLOGY

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION,
WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED
WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC
TECHNOLOGY.

SPC-F005.DWG

REVISIONS				DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398			
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD
			VEE	06-08-10	JAG	11-08-10	XXX



Dimensions : millimetres (Inches)

Specifications:

1. Volts : 24V
2. Watts : 150
3. Filament : CBAR6
4. Base approximate lumens : 4600
5. Approximate color temperature : 3250°K
6. Average life : 100 hours

Part Number Table

Description	Part Number
Microfilm Lamp, GY9.5 Base	DZE

DISCLAIMER:

ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED
HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE
BELIEVE TO BE ACCURATE AND RELIABLE. SINCE
CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE
USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT
FOR THE INTENDED USE AND ASSUME ALL RISK AND
LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

UNLESS OTHERWISE
SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWN BY:	DATE:	DRAWING TITLE:			
VEE	06-08-10	Microfilm Lamp, GY9.5 Base			
CHECKED BY:	DATE:	SIZE	DWG. NO.	ELECTRONIC FILE	
JAG	11-08-10	XXX	XXX	19C8454	REV
APPROVED BY:	DATE:	SCALE:	NTS	U.O.M.: INCHES [mm]	SHEET:
XXX	20-08-10				1 OF 1