


Specifications



Type : Nickel-Metal Hydride Battery			Size : D
Capacity ¹⁾	Typical		10000mAh
	Minimum		9300mAh
Nominal Voltage			1.2V
Charging Current x Time		Fast Charge ²⁾	5000 mA x about 2.2h
Ambient Temp.	Charge Condition	Fast Charge ²⁾	0℃ - 40℃
	Discharge Condition		0℃ - 50℃
	Storage Condition	Less than 30days	-20℃ - 50℃
		Less than 90days	-20℃ - 40℃
		Less than 1year	-20℃ - 30℃
Internal Impedance ³⁾ (after discharge to E.V.=1.0V)			Approx. 5mΩ(at 1000Hz)
Weight ⁴⁾			Approx. 175 g
Size ⁴⁾ :(Diameter) x (Height)			34.0(D) x 59.3(H) mm

1) Single cell capacity under the following condition.

1) Charge : 1000mA×16h, Discharge : 2000mA(E.V.=1.0V) at 20°C


2) Use recommended charging system.

3) After a few charge and discharge cycles under the above 1) condition.

4) With tube.

Typical Characteristics

Charge



Discharge

