





OPT. CODE	RAMP	PACKAGING
A	STD. RAMP	PK-2139-001
C	NONE	

NO. OF CKT'S. 2139-N*-*

VOID CODE NO. CORRESPONDS TO CKT. NO. VOIDED. MULT. VOIDS START WITH 51.

- NOTES:
1. MATERIAL: NYLON, UL94V-2, COLOR: NATURAL
 2. FINISH: N/A
 3. PARTS CONFORM TO PRODUCT SPECIFICATION PS-08-50.
 4. PACKAGING INFORMATION: SEE LEGEND
 5. THIS HOUSING FOR USE WITH TERMINAL NO. 2478 (18 TO 24 GA) & 2578 (22 TO 26 GA). WITH (2.54)±.100 MAX. INSULATION DIA., HOUSING 41695 IS RECOMMENDED FOR OVER (2.54)±.100 DIA. INSULATION.
 6. DIMENSIONS GIVEN ACROSS CENTERLINES ARE SYMMETRICAL ABOUT THOSE CENTERLINES WITHIN HALF THE TOTAL TOLERANCE.
 7. FIRST CKT. NO. ON 2 THRU 5 CKT. HOUSINGS, FIRST AND LAST CKT. NO. ON 6 CKT HOUSING AND LARGER.
 8. MAX BOW .005 MM/MM OR .005 IN/IN
 9. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.

DIM. A	DIM. B	NO. OF CKTS
(7.82)	(3.96±.13)	2
.308	.156±.005	3
(11.79)	(7.92±.13)	
.464	.312±.005	4
(15.75)	(11.89±.13)	
.620	.468±.005	5
(19.71)	(15.85±.13)	
.776	.624±.005	6
(23.67)	(19.81±.13)	
.932	.780±.005	7
(27.64)	(23.77±.13)	
1.088	.936±.005	8
(31.60)	(27.74±.25)	
1.244	1.092±.010	9
(35.56)	(31.70±.25)	
1.400	1.248±.010	10
(39.52)	(35.66±.25)	
1.556	1.404±.010	11
(43.48)	(39.62±.25)	
1.712	1.560±.010	12
(47.45)	(43.59±.25)	
1.868	1.716±.010	13
(51.41)	(47.55±.31)	
2.024	1.872±.012	14
(55.37)	(51.51±.36)	
2.180	2.028±.014	15
(59.33)	(55.47±.36)	
2.336	2.184±.014	16
(63.30)	(59.44±.36)	
2.492	2.340±.014	17
(67.26)	(63.40±.36)	
2.648	2.496±.014	18
(71.22)	(67.36±.36)	
2.804	2.652±.014	19
(75.18)	(71.32±.36)	
2.960	2.808±.014	20
(79.15)	(75.29±.36)	
3.116	2.964±.014	21
(83.11)	(79.25±.46)	
3.272	3.120±.018	22
(87.07)	(83.21±.46)	
3.428	3.276±.018	23
(91.03)	(87.17±.46)	
3.584	3.432±.018	24
(95.00)	(91.14±.46)	
3.740	3.588±.018	

ADD 4.65 REF EC NO. UCP2014-01096 DRAWN BY: 2013/08/06 CHECKED BY: 2013/08/06 APPROVED BY: 2013/08/06 AGT	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± .010 2 PLACES ± 0.25 ± .014 1 PLACE ± 0.36 ± --- 0 PLACE ± ±		DIMENSION STYLE MM/IN DRAWN BY: DATE SAMIEC 1986/01/17 CHECKED BY: DATE PATEL 1986/01/17 APPROVED BY: DATE LENZ 1986/01/07		SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION
		ANGULAR ±1/2° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE CHART		DOCUMENT NO. SD-2139	SHEET NO. 1 OF 2	
		CONNECTOR HOUSING .156 CL CRIMP TERMINAL 2139 SERIES DWG. molex						
		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

