

RF SPLITTER/COMBINER

For RF Return Path Applications in Cable TV
Products and Distribution Equipment : 2-Way; 0°





- Operating bandwidth: 5 MHz to 65 MHz
- Ideal for cable TV distribution equipment and set top box applications
- High Isolation
- Excellent Return Loss
- 235°C peak IR reflow temperature rating

Electrical Specifications @ 25°C — Operating Temperature -40°C to +85°C

Part Number	Frequency (MHz)	Z (Ω)	Isolation 5-65 MHz (dB TYP/MIN)	Return Loss (5-65 MHz)		Insertion Loss (>3dB) 5-65 MHz (dB TYP/MAX)	Phase Unbalance 5-65 MHz (deg MAX)	Amplitude Unbalance 5-65 MHz (dB MAX)
				INPUT (TYP/MIN)	OUTPUT (TYP/MIN)			
CX4004	5 - 65	75	40/26	34/24	31/23	0.22/0.40	1	0.3

Mechanical

CX4004



Power Rating: 1 Watt, MAX

Dimensions: $\frac{\text{Inches}}{\text{mm}}$
Unless otherwise specified, all tolerances are $\pm \frac{.005}{0.13}$

Weight035 grams
Tape & Reel850/reel
Tube65/tube


RF SPLITTER/COMBINER

For RF Return Path Applications in Cable TV
Products and Distribution Equipment : 2-Way; 0°




Typical Performance @ 25°C


INSERTION LOSS




ISOLATION



OUTPUT RETURN LOSS



INPUT RETURN LOSS



For More Information :

UNITED STATES (Worldwide)

12220 World Trade Drive
San Diego, CA 92128
U.S.A.
<http://www.pulseeng.com>
TEL: 858 674 8100
FAX: 858 674 8262

UNITED KINGDOM (Northern Europe)

1 & 2 Huxley Road
The Surrey Research Park
Guildford, Surrey GU2 5RE
United Kingdom
TEL: 44 1483 401700
FAX: 44 1483 401701

FRANCE (Southern Europe)

Zone Industrielle
F-39270
Orgelet
France
TEL: 33 3 84 35 04 04
FAX: 33 3 84 25 46 41

SINGAPORE (Southern Asia)

150 Kampong Ampat
#07-01/02
KA Centre
Singapore 368324
TEL: 65 287 8998
FAX: 65 280 0080

TAIWAN, R.O.C. (Northern Asia)

3F-4, No. 81, Sec. 1
HsinTai Wu Road
Hsi-Chih, Taipei Hsien
Taiwan, R.O.C.
Tel: 886 2 2698 0228
FAX: 886 2 2698 0948

DISTRIBUTOR

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners.