



REVISIONS			
REV	DESCRIPTION	DATE	NAME
A	Initial Release.	07-17-07	AMH
B	Updated temp spec and labeling	08-17-09	AMH

FRONT VIEW



BACK VIEW



- NOTES:
- 1.Operation Temperature:-20°C~+60°C.
 - 2.Storage Temperature:-20°C~+70°C
 - 3.Life Time:>1,000,000 times.
 - 4.Linearity:≤1.5%.
 5. ITO Film:Anti-glare Harding Coating And Anti-Newton Ring
 6. ITO Glass: Sheet Resistance:400±100 Ω/square
 7. Tail Type :Gold plated FPC
 8. All Tolerance Without Marked:±0.3
 9. All Materials and Components must be RoHS compliant
 - 10.No Material is allowed to be larger than the glass size

Pin#	Assignment
Pin1	Top
Pin2	Left
Pin3	Bottom
Pin4	Right



1016 North Lincoln Avenue - Pittsburgh, PA 15233-2302
1.800.366.1904 - 412.322.9900 - Fax: 412.322.9958
e-mail: sales@sawar.com - www.dawar.com

THIS DOCUMENT IS THE PROPERTY OF DAWAR TECHNOLOGIES, INC. AND SHALL NOT BE COPIED, REPRODUCED, DISCLOSED, AND/OR USED AS THE BASIS FOR MANUFACTURING OR SALE WITHOUT PERMISSION OF A DULY AUTHORIZED REPRESENTATIVE OF DAWAR TECHNOLOGIES, INC.

CUSTOMER NAME	UNIT	DAWAR P/N	REV
Standard product offering	mm	FG4_6.5-00001	B
CUSTOMER P/N	REV	DRAWN BY	DATE
		Jason Liao	08-17-09
DESCRIPTION	SHEET	MANUFACTURING NO.	REV
6.5" 4-Wire Resistive Touch Screen	1 OF 1		