




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
GP		00		P	LTR	DESCRIPTION	DATE
				H		REVISED PER ECD-08-007327	27JAN2009



1. THE CONTACT SURFACES OF THE TERMINALS ARE COATED WITH LUBRICANT.
2. ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY UNLESS OTHERWISE SPECIFIED.
3. MATERIAL:
HOUSING - THERMOPLASTIC (BLACK)
TERMINALS - HIGH STRENGTH COPPER ALLOY PLATED WITH EITHER .000030 MIN GOLD OR GOLD FLASH OVER PALLADIUM NICKEL .000030 MIN TOTAL, ON CONTACT MATING SURFACE. .000050 MIN NICKEL UNDERPLATE OVER ENTIRE TERMINAL.
4. WIRE SIZE: 22 AWG SOLID OR 22 AWG 7 STRANDS OF COPPER CONDUCTORS. MAX INSULATION DIAMETER OF .045 IS ACCEPTABLE FOR MOST APPLICATIONS.
5. CORING MAY OR MAY NOT APPEAR AND IS AT THE DISCRETION OF TYCO ELECTRONICS.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DRN G. BOWMAN 2-11-80	Tyco Electronics Corporation Harrisburg, PA 17105-3608
		CHK V.E. SLACK 2-12-80	
DIMENSIONS: INCHES		APPRO B.G. WARD 2-12-80	NAME
TOLERANCES UNLESS OTHERWISE SPECIFIED:		RCPT ASSY, 64 POSITIONS, C SLOT W/ 4-40 TAPPED HOLES, CHAMP-LOK	
0 PLC ± .005		PRODUCT SPEC	
1 PLC ± .005		APPLICATION SPEC	
2 PLC ± .005		SIZE	
3 PLC ± .005		CASE CODE	
4 PLC ± .005		DRAWING NO	
ANGLES ± .005		RESTRICTED TO	
FINISH		A2 00779 C=552307	
MATERIAL		CUSTOMER DRAWING	
		SCALE NTS SHEET 1 OF 1 REV H	