

DATA SHEET

74LVC16244A; 74LVCH16244A
16-bit buffer/line driver; 5 V
input/output tolerant (3-state)

Product specification
Supersedes data of 2002 Oct 30

2003 Jan 30

16-bit buffer/line driver; 5 V input/output tolerant (3-state)

**74LVC16244A;
74LVCH16244A**

FEATURES

- 5 V tolerant inputs/outputs for interfacing with 5 V logic
- Wide supply voltage range from 1.2 to 3.6 V
- CMOS low power consumption
- MULTIBYTE™ flow-through standard pin-out architecture
- Low inductance multiple power and ground pins for minimum noise and ground bounce
- Direct interface with TTL levels
- All data inputs have bushold (74LVCH16244A only).
- Complies with JEDEC standard no. 8-1A
- ESD protection:
HBM EIA/JESD22-A114-A exceeds 2000 V
MM EIA/JESD22-A115-A exceeds 200 V.

DESCRIPTION

The 74LVC(H)16244A is a high-performance, low power, low voltage, Si-gate CMOS device, superior to most advanced CMOS compatible TTL families. Inputs can be driven from either 3.3 or 5 V devices. In 3-state operation, outputs can handle 5 Volt. These features allow the use of these devices as a mixed 3.3 and 5 V environment.

The 74LVC(H)16244A is a 16-bit non-inverting buffer/line driver with 3-state outputs. The device can be used as four 4-bit buffers, two 8-bit buffers or one 16-bit buffer. The 3-state outputs are controlled by the output enable inputs 1OE and 2OE. A HIGH on nOE causes the outputs to assume a high-impedance OFF-state.

The 74LVC(H)16244A is identical to the 74LVC16240A but has non-inverting outputs.

The 74LVCH16244A bushold data inputs eliminates the need for external pull-up resistors to hold unused inputs.

QUICK REFERENCE DATA

GND = 0 V; $T_{amb} = 25\text{ }^{\circ}\text{C}$; $t_r = t_f \leq 2.5\text{ ns}$.

SYMBOL	PARAMETER	CONDITIONS	TYPICAL	UNIT
t_{PHL}/t_{PLH}	propagation delay nA_n to nY_n	$C_L = 50\text{ pF}$; $V_{CC} = 3.3\text{ V}$	3.0	ns
C_i	input capacitance		5.0	pF
C_{PD}	power dissipation capacitance per gate	$V_i = \text{GND to } V_{CC}$; note 1	25	pF

Note

1. C_{PD} is used to determine the dynamic power dissipation (P_D in μW).

$$P_D = C_{PD} \times V_{CC}^2 \times f_i \times N + \Sigma(C_L \times V_{CC}^2 \times f_o) \text{ where:}$$

f_i = input frequency in MHz;

f_o = output frequency in MHz;

C_L = output load capacitance in pF;

V_{CC} = supply voltage in Volts;

N = total switching outputs;

$\Sigma(C_L \times V_{CC}^2 \times f_o)$ = sum of the outputs.

16-bit buffer/line driver; 5 V input/output tolerant
(3-state)

74LVC16244A;
74LVCH16244A

ORDERING INFORMATION

TYPE NUMBER	PACKAGE				
	TEMPERATURE RANGE	PINS	PACKAGE	MATERIAL	CODE
74LVC16244ADL	−40 to +85 °C	48	SSOP48	plastic	SOT370-1
74LVCH16244ADL	−40 to +85 °C	48	SSOP48	plastic	SOT370-1
74LVC16244ADGG	−40 to +85 °C	48	TSSOP48	plastic	SOT362-1
74LVCH16244ADGG	−40 to +85 °C	48	TSSOP48	plastic	SOT362-1
74LVC16244AEV	−40 to +85 °C	56	VFBGA56	plastic	SOT702-1
74LVCH16244AEV	−40 to +85 °C	56	VFBGA56	plastic	SOT702-1

FUNCTION TABLE

See note 1.

INPUT		OUTPUT
$\overline{nOE}$	nA_n	nY_n
L	L	L
L	H	H
H	X	Z

Note

1. H = HIGH voltage level;
L = LOW voltage level;
X = don't care;
Z = high-impedance OFF-state.

16-bit buffer/line driver; 5 V input/output tolerant (3-state)

74LVC16244A;
74LVCH16244A

PINNING

SYMBOL	PINS	BALLS	DESCRIPTION
1 $\overline{\text{OE}}$	1	A1	output enable input (active LOW)
n.c.	–	A2, A3, A4, A5, E3, E4, F3, F4, K2, K3, K4, K5	not connected
1Y ₀	2	B2	data output
1Y ₁	3	B1	data output
GND	4, 10, 15, 21, 28, 34, 39, 45	B3, B4, D3, D4, G3, G4, J3, J4	ground (0 V)
1Y ₂	5	C2	data output
1Y ₃	6	C1	data output
V _{CC}	7, 18, 31, 42	C3, H3, C4, H4	supply voltage
2Y ₀	8	D2	data output
2Y ₁	9	D1	data output
2Y ₂	11	E2	data output
2Y ₃	12	E1	data output
3Y ₀	13	F1	data output
3Y ₁	14	F2	data output
3Y ₂	16	G1	data output
3Y ₃	17	G2	data output
4Y ₀	19	H1	data output
4Y ₁	20	H2	data output
4Y ₂	22	J1	data output
4Y ₃	23	J2	data output
4 $\overline{\text{OE}}$	24	K1	output enable input (active LOW)
3 $\overline{\text{OE}}$	25	K6	output enable input (active LOW)
4A ₃	26	J5	data input
4A ₂	27	J6	data input
4A ₁	29	H5	data input
4A ₀	30	H6	data input
3A ₃	32	G5	data input
3A ₂	33	G6	data input
3A ₁	35	F5	data input
3A ₀	36	F6	data input
2A ₃	37	D6	data input
2A ₂	38	E5	data input
2A ₁	40	D6	data input
2A ₀	41	D5	data input
1A ₃	43	C6	data input
1A ₂	44	C5	data input
1A ₁	46	B6	data input
1A ₀	47	B5	data input
2 $\overline{\text{OE}}$	48	A6	output enable input (active LOW)

16-bit buffer/line driver; 5 V input/output tolerant
(3-state)

74LVC16244A;
74LVCH16244A




Fig.1 Pin configuration SSOP/TSSOP48.

A	1OE					2OE
B	1Y1	1Y0	GND	GND	1A0	1A1
C	1Y3	1Y2	VCC	VCC	1A2	1A3
D	2Y1	2Y0	GND	GND	2A0	2A1
E	2Y3	2Y2			2A2	2A3
F	3Y0	3Y1			3A1	3A0
G	3Y2	3Y3	GND	GND	3A3	3A2
H	4Y0	4Y1	VCC	VCC	4A1	4A0
J	4Y2	4Y3	GND	GND	4A3	4A2
K	4OE					3OE
	1	2	3	4	5	6

MNA702

Fig.2 Pin configuration VFBGA56.

16-bit buffer/line driver; 5 V input/output tolerant (3-state)

74LVC16244A;
74LVCH16244A




Fig.3 Logic symbol.

16-bit buffer/line driver; 5 V input/output tolerant
(3-state)

74LVC16244A;
74LVCH16244A




Fig.4 Logic symbol (IEEE/IEC).




Fig.5 Bushold circuit.

16-bit buffer/line driver; 5 V input/output tolerant (3-state)

74LVC16244A;
74LVCH16244A

RECOMMENDED OPERATING CONDITIONS

SYMBOL	PARAMETER	CONDITIONS	MIN.	MAX.	UNIT
V _{CC}	supply voltage	for maximum speed performance	2.7	3.6	V
		for low voltage applications	1.2	3.6	V
V _I	input voltage		0	5.5	V
V _O	output voltage	output HIGH or LOW state	0	V _{CC}	V
		output 3-state	0	5.5	V
T _{amb}	operating ambient temperature	in free air	−40	+85	°C
t _r , t _f	input rise and fall times	V _{CC} = 1.2 to 2.7 V	0	20	ns/V
		V _{CC} = 2.7 to 3.6 V	0	10	ns/V

LIMITING VALUES

In accordance with the Absolute Maximum Rating System (IEC 60134); voltages are referenced to GND (ground = 0 V).

SYMBOL	PARAMETER	CONDITIONS	MIN.	MAX.	UNIT
V _{CC}	supply voltage		−0.5	+6.5	V
I _{IK}	input diode current	V _I < 0	–	−50	mA
V _I	input voltage	note 1	−0.5	+6.5	V
I _{OK}	output diode current	V _O > V _{CC} or V _O < 0	–	±50	mA
V _O	output voltage	output HIGH or LOW state; note 1	−0.5	V _{CC} + 0.5	V
		output 3-state; note 1	−0.5	+6.5	V
I _O	output source or sink current	V _O = 0 to V _{CC}	–	±50	mA
I _{CC} , I _{GND}	V _{CC} or GND current		–	±100	mA
T _{stg}	storage temperature		−65	+150	°C
P _{tot}	power dissipation; SSOP and TSSOP package	temperature range from −40 to +85 °C; note 2	–	500	mW
	VFBGA package	temperature range from −40 to +85 °C; note 3	–	1000	mW

Notes

1. The input and output voltage ratings may be exceeded if the input and output current ratings are observed.
2. Above 60 °C the value of P_D derates linearly with 5.5 mW/K.
3. Above 70 °C the value of P_D derates linearly with 1.8 mW/K.

16-bit buffer/line driver; 5 V input/output tolerant (3-state)

74LVC16244A;
74LVCH16244A

DC CHARACTERISTICS

At recommended operating conditions; voltage are referenced to GND (ground = 0 V).

SYMBOL	PARAMETER	TEST CONDITIONS		MIN.	TYP. ⁽¹⁾	MAX.	UNIT
		OTHER	V _{CC} (V)				
T _{amb} = –40 to +85 °C							
V _{IH}	HIGH-level input voltage		1.2	V _{CC}	–	–	V
			2.7 to 3.6	2.0	–	–	V
V _{IL}	LOW-level input voltage		1.2	–	–	GND	V
			2.7 to 3.6	–	–	0.8	V
V _{OH}	HIGH-level output voltage	V _I = V _{IH} or V _{IL} I _O = –12 mA I _O = –100 μA I _O = –18 mA I _O = –24 mA	2.7	V _{CC} – 0.5	–	–	V
			3.0	V _{CC} – 0.2	V _{CC}	–	V
			3.0	V _{CC} – 0.6	–	–	V
			3.0	V _{CC} – 0.8	–	–	V
V _{OL}	LOW-level output voltage	V _I = V _{IH} or V _{IL} I _O = 12 mA I _O = 100 μA I _O = 24 mA	2.7	–	–	0.40	V
			3.0	–	–	0.20	V
			3.0	–	–	0.55	V
I _I	input leakage current	V _I = 5.5 V or GND; note 2	3.6	–	±0.1	±5	μA
I _{OZ}	3-state output OFF-state current	V _I = V _{IH} or V _{IL} ; V _O = 5.5 V or GND	3.6	–	0.1	±5	μA
I _{off}	power off leakage supply	V _I or V _O = 5.5 V	0.0	–	0.1	±10	μA
I _{CC}	quiescent supply current	V _I = V _{CC} or GND; I _O = 0	3.6	–	0.1	20	μA
ΔI _{CC}	additional quiescent supply current per pin	V _I = V _{CC} –0.6V; I _O = 0	2.7 to 3.6	–	5	500	μA
I _{BHL}	bushold LOW sustaining current	V _I = 0.8 V; notes 3, 4 and 5	3.0	75	–	–	μA
I _{BHH}	bushold HIGH sustaining current	V _I = 2.0 V; notes 3, 4 and 5	3.0	–75	–	–	μA
I _{BHLO}	bushold LOW overdrive current	notes 3, 4 and 6	3.6	500	–	–	μA
I _{BHHO}	bushold HIGH overdrive current	notes 3, 4 and 6	3.6	–500	–	–	μA

Notes

1. All typical values are measured at V_{CC} = 3.3 V and T_{amb} = 25 °C.
2. For bushold parts, the bushold circuit is switched off when V_I > V_{CC} allowing 5.5 V on the input terminal.
3. Valid for data inputs of bushold parts (74LVCH16244A) only.
4. For data inputs only, control inputs do not have a bushold circuit.
5. The specified sustaining current at the data input holds the input below the specified V_I level.
6. The specified overdrive current at the data input forces the data input to the opposite input state.

16-bit buffer/line driver; 5 V input/output tolerant
(3-state)

74LVC16244A;
74LVCH16244A

AC CHARACTERISTICS


GND = 0 V; $t_r = t_f \leq 2.5$ ns.

SYMBOL	PARAMETER	CONDITIONS		MIN.	TYP.	MAX.	UNIT
		WAVEFORMS	V _{CC} (V)				
T _{amb} = −40 to +85 °C							
t _{PHL} /t _{PLH}	propagation delay nA _n to nY _n	see Figs 6 and 8	1.2	–	11.0	–	ns
			2.7	1.5	–	5.5	ns
			3.0 to 3.6	1.5	3.0 ⁽¹⁾	4.5	ns
t _{PZH} /t _{PZL}	3-state output enable time n $\overline{\text{OE}}$ to nY _n	see Figs 7 and 8	1.2	–	15.0	–	ns
			2.7	1.5	–	6.5	ns
			3.0 to 3.6	1.5	3.5 ⁽¹⁾	5.5	ns
t _{PHZ} /t _{PLZ}	3-state output disable time n $\overline{\text{OE}}$ to nY _n	see Figs 7 and 8	1.2	–	10.0	–	ns
			2.7	1.5	–	6.2	ns
			3.0 to 3.6	1.5	3.7 ⁽¹⁾	5.2	ns

Note


1. Typical values are measured at V_{CC} = 3.3 V and T_{amb} = 25 °C.

AC WAVEFORMS



16-bit buffer/line driver; 5 V input/output tolerant
(3-state)

74LVC16244A;
74LVCH16244A



V_{CC}	V_M	INPUT	
		V_I	$t_r = t_f$
1.2 V	$0.5 \times V_{CC}$	V_{CC}	≤ 2.5 ns
2.7 V	1.5 V	2.7 V	≤ 2.5 ns
3.0 to 3.6 V	1.5 V	2.7 V	≤ 2.5 ns


$$\begin{aligned} V_X &= V_{OL} + 0.3 \text{ V at } V_{CC} \geq 2.7 \text{ V;} \\ V_X &= V_{OL} + 0.1 \text{ V at } V_{CC} < 2.7 \text{ V;} \\ V_Y &= V_{OH} - 0.3 \text{ V at } V_{CC} \geq 2.7 \text{ V;} \\ V_Y &= V_{OH} - 0.1 \text{ V at } V_{CC} < 2.7 \text{ V.} \end{aligned}$$

V_{OL} and V_{OH} are typical output voltage drop that occur with the output load.

Fig.7 3-state enable and disable times.

16-bit buffer/line driver; 5 V input/output tolerant
(3-state)

74LVC16244A;
74LVCH16244A



VCC	VI	CL	RL	VEXT		
				tPLH/tPHL	tPZH/tPHZ	tPZL/tPLZ
1.2 V	VCC	50 pF	500 Ω	open	GND	2 × VCC
2.7 V	2.7 V	50 pF	500 Ω	open	GND	2 × VCC
3.0 to 3.6 V	2.7 V	50 pF	500 Ω	open	GND	2 × VCC

Definitions for test circuits:
RL = Load resistor.
CL = Load capacitance including jig and probe capacitance.
RT = Termination resistance should be equal to the output impedance Z0 of the pulse generator.

Fig.8 Load circuitry for switching times.


16-bit buffer/line driver; 5 V input/output tolerant
(3-state)

74LVC16244A;
74LVCH16244A

PACKAGE OUTLINES

SSOP48: plastic shrink small outline package; 48 leads; body width 7.5 mm

SOT370-1




16-bit buffer/line driver; 5 V input/output tolerant
(3-state)

74LVC16244A;
74LVCH16244A

TSSOP48: plastic thin shrink small outline package; 48 leads; body width 6.1 mm

SOT362-1




16-bit buffer/line driver; 5 V input/output tolerant
(3-state)

74LVC16244A;
74LVCH16244A

VFBGA56: plastic very thin fine-pitch ball grid array package; 56 balls; body 4.5 x 7 x 0.65 mm

SOT702-1



16-bit buffer/line driver; 5 V input/output tolerant (3-state)

74LVC16244A;
74LVCH16244A

SOLDERING

Introduction to soldering surface mount packages

This text gives a very brief insight to a complex technology. A more in-depth account of soldering ICs can be found in our *"Data Handbook IC26; Integrated Circuit Packages"* (document order number 9398 652 90011).

There is no soldering method that is ideal for all surface mount IC packages. Wave soldering can still be used for certain surface mount ICs, but it is not suitable for fine pitch SMDs. In these situations reflow soldering is recommended.

Reflow soldering

Reflow soldering requires solder paste (a suspension of fine solder particles, flux and binding agent) to be applied to the printed-circuit board by screen printing, stencilling or pressure-syringe dispensing before package placement.

Several methods exist for reflowing; for example, convection or convection/infrared heating in a conveyor type oven. Throughput times (preheating, soldering and cooling) vary between 100 and 200 seconds depending on heating method.

Typical reflow peak temperatures range from 215 to 250 °C. The top-surface temperature of the packages should preferably be kept below 220 °C for thick/large packages, and below 235 °C for small/thin packages.

Wave soldering

Conventional single wave soldering is not recommended for surface mount devices (SMDs) or printed-circuit boards with a high component density, as solder bridging and non-wetting can present major problems.

To overcome these problems the double-wave soldering method was specifically developed.

If wave soldering is used the following conditions must be observed for optimal results:

- Use a double-wave soldering method comprising a turbulent wave with high upward pressure followed by a smooth laminar wave.
- For packages with leads on two sides and a pitch (e):
 - larger than or equal to 1.27 mm, the footprint longitudinal axis is **preferred** to be parallel to the transport direction of the printed-circuit board;
 - smaller than 1.27 mm, the footprint longitudinal axis **must** be parallel to the transport direction of the printed-circuit board.

The footprint must incorporate solder thieves at the downstream end.

- For packages with leads on four sides, the footprint must be placed at a 45° angle to the transport direction of the printed-circuit board. The footprint must incorporate solder thieves downstream and at the side corners.

During placement and before soldering, the package must be fixed with a droplet of adhesive. The adhesive can be applied by screen printing, pin transfer or syringe dispensing. The package can be soldered after the adhesive is cured.

Typical dwell time is 4 seconds at 250 °C.

A mildly-activated flux will eliminate the need for removal of corrosive residues in most applications.

Manual soldering

Fix the component by first soldering two diagonally-opposite end leads. Use a low voltage (24 V or less) soldering iron applied to the flat part of the lead. Contact time must be limited to 10 seconds at up to 300 °C.

When using a dedicated tool, all other leads can be soldered in one operation within 2 to 5 seconds between 270 and 320 °C.

16-bit buffer/line driver; 5 V input/output tolerant
(3-state)

74LVC16244A;
74LVCH16244A

Suitability of surface mount IC packages for wave and reflow soldering methods

PACKAGE ⁽¹⁾	SOLDERING METHOD	
	WAVE	REFLOW ⁽²⁾
BGA, LBGA, LFBGA, SQFP, TFBGA, VFBGA	not suitable	suitable
DHVQFN, HBCC, HBGA, HLQFP, HSQFP, HSOP, HTQFP, HTSSOP, HVQFN, HVSON, SMS	not suitable ⁽³⁾	suitable
PLCC ⁽⁴⁾ , SO, SOJ	suitable	suitable
LQFP, QFP, TQFP	not recommended ⁽⁴⁾⁽⁵⁾	suitable
SSOP, TSSOP, VSO, VSSOP	not recommended ⁽⁶⁾	suitable

Notes

1. For more detailed information on the BGA packages refer to the “(LF)BGA Application Note” (AN01026); order a copy from your Philips Semiconductors sales office.
2. All surface mount (SMD) packages are moisture sensitive. Depending upon the moisture content, the maximum temperature (with respect to time) and body size of the package, there is a risk that internal or external package cracks may occur due to vaporization of the moisture in them (the so called popcorn effect). For details, refer to the Drypack information in the “Data Handbook IC26; Integrated Circuit Packages; Section: Packing Methods”.
3. These packages are not suitable for wave soldering. On versions with the heatsink on the bottom side, the solder cannot penetrate between the printed-circuit board and the heatsink. On versions with the heatsink on the top side, the solder might be deposited on the heatsink surface.
4. If wave soldering is considered, then the package must be placed at a 45° angle to the solder wave direction. The package footprint must incorporate solder thieves downstream and at the side corners.
5. Wave soldering is suitable for LQFP, TQFP and QFP packages with a pitch (e) larger than 0.8 mm; it is definitely not suitable for packages with a pitch (e) equal to or smaller than 0.65 mm.
6. Wave soldering is suitable for SSOP and TSSOP packages with a pitch (e) equal to or larger than 0.65 mm; it is definitely not suitable for packages with a pitch (e) equal to or smaller than 0.5 mm.

16-bit buffer/line driver; 5 V input/output tolerant (3-state)

74LVC16244A;
74LVCH16244A

DATA SHEET STATUS

LEVEL	DATA SHEET STATUS ⁽¹⁾	PRODUCT STATUS ⁽²⁾⁽³⁾	DEFINITION
I	Objective data	Development	This data sheet contains data from the objective specification for product development. Philips Semiconductors reserves the right to change the specification in any manner without notice.
II	Preliminary data	Qualification	This data sheet contains data from the preliminary specification. Supplementary data will be published at a later date. Philips Semiconductors reserves the right to change the specification without notice, in order to improve the design and supply the best possible product.
III	Product data	Production	This data sheet contains data from the product specification. Philips Semiconductors reserves the right to make changes at any time in order to improve the design, manufacturing and supply. Relevant changes will be communicated via a Customer Product/Process Change Notification (CPCN).

Notes

1. Please consult the most recently issued data sheet before initiating or completing a design.
2. The product status of the device(s) described in this data sheet may have changed since this data sheet was published. The latest information is available on the Internet at URL <http://www.semiconductors.philips.com>.
3. For data sheets describing multiple type numbers, the highest-level product status determines the data sheet status.

DEFINITIONS

Short-form specification — The data in a short-form specification is extracted from a full data sheet with the same type number and title. For detailed information see the relevant data sheet or data handbook.

Limiting values definition — Limiting values given are in accordance with the Absolute Maximum Rating System (IEC 60134). Stress above one or more of the limiting values may cause permanent damage to the device. These are stress ratings only and operation of the device at these or at any other conditions above those given in the Characteristics sections of the specification is not implied. Exposure to limiting values for extended periods may affect device reliability.

Application information — Applications that are described herein for any of these products are for illustrative purposes only. Philips Semiconductors make no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

DISCLAIMERS

Life support applications — These products are not designed for use in life support appliances, devices, or systems where malfunction of these products can reasonably be expected to result in personal injury. Philips Semiconductors customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Philips Semiconductors for any damages resulting from such application.

Right to make changes — Philips Semiconductors reserves the right to make changes in the products - including circuits, standard cells, and/or software - described or contained herein in order to improve design and/or performance. When the product is in full production (status 'Production'), relevant changes will be communicated via a Customer Product/Process Change Notification (CPCN). Philips Semiconductors assumes no responsibility or liability for the use of any of these products, conveys no licence or title under any patent, copyright, or mask work right to these products, and makes no representations or warranties that these products are free from patent, copyright, or mask work right infringement, unless otherwise specified.

16-bit buffer/line driver; 5 V input/output tolerant
(3-state)

74LVC16244A;
74LVCH16244A

NOTES

Philips Semiconductors – a worldwide company

Contact information

For additional information please visit <http://www.semiconductors.philips.com>. Fax: **+31 40 27 24825**

For sales offices addresses send e-mail to: sales.addresses@www.semiconductors.philips.com.

© Koninklijke Philips Electronics N.V. 2003

SCA75

All rights are reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.

The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Printed in The Netherlands

613508/06/pp20

Date of release: 2003 Jan 30

Document order number: 9397 750 10748

Let's make things better.

**Philips
Semiconductors**



PHILIPS