

General Purpose Tweezers

Handcrafted to perfect tip symmetry and balance, polished edges, superior no-scratch/antiglare satin finish
The right tweezers and material for a successful application.



119.SA

6" 150mm
fine tips, serrated tips and grips



119A.SA

6" 150mm
as 119, strong, serrated tips and grips



120A.SA

4 1/4" 110mm
fine, strong serrated tips and grips



121.SA

6 1/4" 160mm
very strong, blunt serrated tips and grips



121M.SA

6 1/4" 160mm
as 120, thin serrated tips and serrated grips



122.SA

6" 150mm
fine, bent serrated tips and grips



123.SA

6" 150mm
Fine, double bent serrated tips and grips



124.SA

6" 150mm
as 122, strong serrated tips and serrated grips



231.SA

4 3/4" 120mm
fine, serrated tips



321.SA

4 3/4" 120mm
flat rounded tips PTFE coated



456.SA

5" 130mm
fine serrated tips



475.SA

5 1/2" 140mm
strong blunt precision serrated tips and serrated grips

647.SA
647.S

4 3/4" 120mm
strong blunt precision tips serrated tips and grips

648.SA
648.S

6" 150mm
strong, fine, alignment pin serrated tips and grips

649.SA
649.S

6" 150mm
strong, fine, bent, alignment pin serrated tips and grips




PB.NP

5 3/4" 145mm; 0.14" 3.6mm
nickel plated tweezers to hold pearls and ball bearings

Boley Tweezers

Ergonomic, general purpose tweezers available in different materials for specific applications.

AA.SA
AA.S
AA.NP
AA.TA

5" 130mm
general purpose straight fine tips

GG.SA
GG.NP

5" 130mm very slim tips, max visibility

MM.SA
MM.NP

5" 130mm
general purpose strong fine tips

NN.SA
NN.NP

4 1/2" 115mm
as MM, short

RR.SA
RR.NP

5 3/4" 145mm
heavy duty tweezers strong tips, rounded edges



D.NP

3 3/4" 95mm
cutting nickel plated tweezers rounded edges

SMD Tweezers

Smooth handling and positioning of all SMD components. Different tips and angles for specific jobs. Satin antiglare finish and ergonomic design. Modifications or special models available on request. Available as reverse action model.



SM100.SA

4 1/2" 115mm
reverse action for handling PCBs with SMDs



SM101.SA

4 1/2" 115mm
reverse action for soldering and de-soldering
8, 14 or 16 Lead SMDs



SM102.SA

4 1/2" 115mm
reverse action for soldering and de-soldering 20, 28, 44 and
68 LCCC and PLCC pad devices




SM103.SA

4 1/2" 115mm
for handling and positioning 2 and 3 lead SOT
packages at 45° angle




SM104.SA

4 3/4" 120mm
for handling and positioning 3 lead SOT packages,
monolithic chip capacitors, etc.



SM105.SA

4 3/4" 120mm
special design for positioning all SOT packages vertically



SM106.SA

4 3/4" 120mm
for positioning all SOT packages horizontally.
With flat base tips (4 mm long)




SM107.SA

4 3/4" 120mm
for positioning all flat devices at 60° angle.



SM108.SA

4 3/4" 120mm
for positioning and soldering 1mm wide components.
tips are grooved inside



SM109.SA

4 3/4" 120mm
same as SM 108 but with 45° tips without anti-crush feature




SM110.SA

4 3/4" 120mm
for positioning monolithic chips capacitors, grooved tips



SM111.SA

4 3/4" 120mm
for positioning 5 mm monolithic chip capacitors
with flat base grooved tips (2 mm long)



SM112.SA

4 3/4" 120mm
for positioning 5 mm monolithic chip capacitors at 60°.
Grooved tips



SM113.SA

4 3/4" 120mm
3mm long tips bent at 60° angle one forked blade lead entry




SM114.SA

4 3/4" 120mm
same as SM113 but with straight tips for vertical holding



SM115.SA

4 3/4" 120mm
grooved tips at 30° angle for holding and positioning
cylindrical devices (up to 1 mm diam.)



SM116.SA

4 3/4" 120mm
grooved straight tips. for vertical positioning
of cylindrical devices (up to 1 mm diam. or more)



SM117.SA

4 3/4" 120mm
for positioning SOT packages at 30° angle



K5SMD.SA

SMD precision tweezers set
SM103, SM107, SM108, SM111, SM115
top quality hard/foam wallet