


Part Number : **550203**

Type	Size	Rating	Description
Incandescent	T10	14V 270mA	T-3¼ Wedgebase lamp

Dimensions(mm):



TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
14	243	275	297	20	25	30	2500

Notes:

- W2.1x9.5d in accordance with IEC 61-1, (BS EN 60061-1), sheet 7004-91-x.
- C-2F filament shape.
- Lamp marking (two line) **VCH XY** where XY is a manufacturing date code
194
- Bead colour: BLUE
- RoHS and REACH SVHC compliant

Issue # 1 : 6 Jun 11