




DESCRIPTION: 44-PIN MALE / MALE HIGH DENSITY GENDER CHANGER




SPECIFICATION:

INSULATOR: PBT GLASS FIBER REINFORCED UL 94VO  
CONTACT: BRASS  
CONTACT PLATING: GOLD PLATED OVER NICKEL  
SHELL: TIN PLATED SHELL  
CURRENT RATING: 3 AMP  
DIELECTRIC STRENGTH: 1,000VAC FOR 1 MINUTE  
INSULATION RESISTANCE: 1,000 MegOHMS MIN @500 VDC  
TEMPERATURE: -55° C - +105° C

NOTE:

LABEL: YELLOW COLOR WITH BLACK CHARACTORS  
ONE SIDE: MINI GENDER CHANGER  
OTHER SIDE: U.S.A. PATENT 5199906



| 44-PIN MALE |     | 44-PIN MALE |
|-------------|-----|-------------|
| 1           | --- | 1           |
| 2           | --- | 2           |
| 3           | --- | 3           |
| ...         |     |             |
| 43          | --- | 43          |
| 44          | --- | 44          |
| SHELL       | --- | SHELL       |

PIN OUT

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: C. SMITH

DATE: 10-15-07

CHECKED:

DATE:

SCALE: 1.5 : 1

SHEET 1 OF 1

REV 1

DWG NO.

GCHDLP44M44M

RoHS COMPLIANT

NorComp