







OPTION A



PCB LAYOUT: COMPONENT SIDE
TYPICAL PCB THICKNESS: 2.36/.093



NOTES:

- MATERIAL: SHROUDED WAFER: GLASS FILLED, LIQUID CRYSTAL POLYMER, COLOR: BLACK, 94V-0.
- PINS: COPPER ALLOY.
- PLATING:
 - TIN 0.000381/.000150 MINIMUM TIN, OVER NICKEL UNDERPLATE OVERALL
 - 15 GOLD 0.000381/.000015 MINIMUM GOLD PLATE IN SELECTED AREA
 - 0.00191/.000075 MINIMUM TIN IN SELECTED AREA
 - OVER NICKEL UNDERPLATE OVERALL
 - 30 GOLD 0.00076/.000030 MINIMUM GOLD PLATE IN SELECTED AREA
 - 0.00191/.000075 MINIMUM TIN IN SELECTED AREA,
 - OVER NICKEL UNDERPLATE OVERALL
- PRODUCT SPECIFICATION: PS-70567.
- PACKAGING: SEE CHARTS
- MEASURE POINT FOR PLATING THICKNESS.
- PIN PUSHOUT FORCE: 4 LBS. MINIMUM IN DIRECTION INDICATED.
- FOR ILLUSTRATION PURPOSES, 20 (DUAL 10) CIRCUIT SIZE HEADER SHOWN.
- PIN SOLDERABILITY PER MOLEX SPEC. SMES-152.
- WINDOW NOT AVAILABLE ON 6 OR 8 CIRCUIT SIZE.
- THIS PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.

CORRECT PCB HOLE SIZE
EC NO: UCP2011-0294
2010/08/02
DRWN:MS BARRA
CHKD:JORGAN
1988/03/10
APPR:MBANAKIS
2010/08/03

QUALITY SYMBOLS
▽=0
▽=0
▽=0







GENERAL TOLERANCES (UNLESS SPECIFIED)
mm INCH
4 PLACES ± --- ± ---
3 PLACES ± --- ± .005
2 PLACES ± 0.13 ± .010
1 PLACE ± 0.25 ± ---
ANGULAR ± 1/2°
DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN
DRAWN BY DATE
EIK 1988/03/10
CHECKED BY DATE
EIK 1988/03/10
APPROVED BY DATE
SMILLER 2010/03/31
MATERIAL NO.
SEE TABLE
SIZE C


SCALE
4:1
DESIGN UNITS
INCH
THIRD ANGLE PROJECTION
4 SIDES SHROUDED HEADER
HIGH TEMP, (2.54)/.100
GRID W/ (.064)/.025 PINS
MOLEX INCORPORATED
SDA-70567-****
SHEET NO.
1 OF 5
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

CKT	DIM A	DIM B	DIM L	DIM M	DIM N
06	8.43 .332	5.08 .200	1.68 .066	1.68 .066	
08	10.97 .432	7.62 .300	1.68 .066	1.68 .066	
10	13.51 .532	10.16 .400	1.68 .066	4.22 .166	
12	16.05 .632	12.70 .500	1.68 .066	4.22 .166	
14	18.59 .732	15.24 .600	1.68 .066	6.76 .266	
16	21.13 .832	17.78 .700	1.68 .066	6.76 .266	
18	23.67 .932	20.32 .800	1.68 .066	9.30 .366	
20	26.21 1.032	22.86 .900	1.68 .066	1.68 .066	19.46 .766
22	28.75 1.132	25.40 1.000	1.68 .066	1.68 .066	22.00 .866
24	31.29 1.232	27.94 1.100	1.68 .066	1.68 .066	24.54 .966
26	33.83 1.332	30.48 1.200	1.68 .066	1.68 .066	27.08 1.066
28	36.37 1.432	33.02 1.300	1.68 .066	1.68 .066	29.62 1.166
30	38.91 1.532	35.56 1.400	1.68 .066	1.68 .066	32.16 1.266
32	41.45 1.632	38.10 1.500	1.68 .066	1.68 .066	34.70 1.366
34	43.99 1.732	40.64 1.600	1.68 .066	1.68 .066	37.24 1.466
36	46.53 1.832	43.18 1.700	1.68 .066	1.68 .066	39.78 1.566
38	49.07 1.932	45.72 1.800	1.68 .066	1.68 .066	42.32 1.666
40	51.61 2.032	48.26 1.900	1.68 .066	1.68 .066	44.86 1.766
42	54.15 2.132	50.80 2.000	1.68 .066	1.68 .066	47.40 1.866
44	56.69 2.232	53.34 2.100	1.68 .066	1.68 .066	49.94 1.966
46	59.23 2.332	55.88 2.200	1.68 .066	1.68 .066	52.48 2.066
48	61.77 2.432	58.42 2.300	1.68 .066	1.68 .066	55.02 2.166
50	64.31 2.532	60.96 2.400	1.68 .066	1.68 .066	57.56 2.266
52	66.85 2.632	63.50 2.500	1.68 .066	1.68 .066	60.10 2.366
54	69.39 2.732	66.04 2.600	1.68 .066	1.68 .066	62.64 2.466
56	71.93 2.832	68.58 2.700	1.68 .066	1.68 .066	65.18 2.566
58	74.47 2.932	71.12 2.800	1.68 .066	1.68 .066	67.72 2.666
60	77.01 3.032	73.66 2.900	1.68 .066	1.68 .066	70.26 2.766
62	79.55 3.132	76.20 3.000	1.68 .066	1.68 .066	72.80 2.866
64	82.09 3.232	78.74 3.100	1.68 .066	1.68 .066	75.34 2.966
66	84.63 3.332	81.28 3.200	1.68 .066	1.68 .066	77.88 3.066
68	87.17 3.432	83.82 3.300	1.68 .066	1.68 .066	80.42 3.166
70	89.71 3.532	86.36 3.400	1.68 .066	1.68 .066	82.96 3.266
72	92.25 3.632	88.90 3.500	1.68 .066	1.68 .066	85.50 3.366

OPTION B



PCB LAYOUT: COMPONENT SIDE
TYPICAL PCB THICKNESS: 2.36/.093



SECTION Y-Y

NOTES:

1. MATERIAL: SHROUDED WAFER: 30% G.F. LCP, COLOR: BLACK, 94V-0. PINS: COPPER ALLOY.
2. PLATING:
TIN - (0.00381)/.000150 MINIMUM TIN OVER NICKEL UNDERPLATE OVERALL
15 GOLD - (0.000381)/.000015 MINIMUM GOLD PLATE IN SELECTED AREA
(0.00191)/.000075 MINIMUM TIN IN SELECTED AREA,
OVER NICKEL UNDERPLATE OVERALL
30 GOLD - (0.000761)/.000030 MINIMUM GOLD PLATE IN SELECTED AREA
(0.00191)/.000075 MINIMUM TIN IN SELECTED AREA,
OVER NICKEL UNDERPLATE OVERALL
3. PRODUCT SPECIFICATION: PS-70567.
4. PACKAGING: SEE CHARTS
5. PIN PUSHOUT FORCE: 4 LBS. MIN IN DIRECTION INDICATED.
6. FOR ILLUSTRATION PURPOSES, 20 (DUAL 10) CIRCUIT SIZE HEADER SHOWN.
7. PIN SOLDERABILITY PER MOLEX SPEC. SMES-152.
8. MEASURE POINT FOR PLATING THICKNESS.
9. WINDOW IS NOT AVAILABLE ON 6 CIRCUIT.
10. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.
11. SEE SHEET 1 FOR ALL OTHER DIMENSIONS

CKT	DIM A	DIM B	DIM L	DIM M	DIM N
06	12.70 .500	5.08 .200	3.81 .150	3.81 .150	—
08	15.24 .600	7.62 .300	3.81 .150	3.81 .150	—
10	17.78 .700	10.16 .400	3.81 .150	6.35 .250	—
12	20.32 .800	12.70 .500	3.81 .150	6.35 .250	—
14	22.86 .900	15.24 .600	3.81 .150	8.89 .350	—
16	25.40 1.000	17.78 .700	3.81 .150	8.89 .350	—
18	27.94 1.100	20.32 .800	3.81 .150	11.43 .450	—
20	30.48 1.200	22.86 .900	3.81 .150	3.81 .150	21.59 .850
22	33.02 1.300	25.40 1.000	3.81 .150	3.81 .150	24.13 .950
24	35.56 1.400	27.94 1.100	3.81 .150	3.81 .150	26.67 1.050
26	38.10 1.500	30.48 1.200	3.81 .150	3.81 .150	29.21 1.150
28	40.64 1.600	33.02 1.300	3.81 .150	3.81 .150	31.75 1.250
30	43.18 1.700	35.56 1.400	3.81 .150	3.81 .150	34.29 1.350
32	45.72 1.800	38.10 1.500	3.81 .150	3.81 .150	36.83 1.450
34	48.26 1.900	40.64 1.600	3.81 .150	3.81 .150	39.37 1.550
36	50.80 2.000	43.18 1.700	3.81 .150	3.81 .150	41.91 1.650
38	53.34 2.100	45.72 1.800	3.81 .150	3.81 .150	44.45 1.750
40	55.88 2.200	48.26 1.900	3.81 .150	3.81 .150	46.99 1.850
42	58.42 2.300	50.80 2.000	3.81 .150	3.81 .150	49.53 1.950
44	60.96 2.400	53.34 2.100	3.81 .150	3.81 .150	52.07 2.050
46	63.50 2.500	55.88 2.200	3.81 .150	3.81 .150	54.61 2.150
48	66.04 2.600	58.42 2.300	3.81 .150	3.81 .150	57.15 2.250
50	68.58 2.700	60.96 2.400	3.81 .150	3.81 .150	59.69 2.350
52	71.12 2.800	63.50 2.500	3.81 .150	3.81 .150	62.23 2.450
54	73.66 2.900	66.04 2.600	3.81 .150	3.81 .150	64.77 2.550
56	76.20 3.000	68.58 2.700	3.81 .150	3.81 .150	67.31 2.650
58	78.74 3.100	71.12 2.800	3.81 .150	3.81 .150	69.85 2.750
60	81.28 3.200	73.66 2.900	3.81 .150	3.81 .150	72.39 2.850
62	83.82 3.300	76.20 3.000	3.81 .150	3.81 .150	74.93 2.950
64	86.36 3.400	78.74 3.100	3.81 .150	3.81 .150	77.47 3.050
66	88.90 3.500	81.28 3.200	3.81 .150	3.81 .150	80.01 3.150
68	91.44 3.600	83.82 3.300	3.81 .150	3.81 .150	82.55 3.250
70	93.98 3.700	86.36 3.400	3.81 .150	3.81 .150	85.09 3.350
72	96.52 3.800	88.90 3.500	3.81 .150	3.81 .150	87.63 3.450

CORRECT PCB HOLE SIZE		QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	TITLE	DOCUMENT NO.	SHEET NO.
EC NO:	DATE		mm	INCH	MM/IN	DATE						
UCP2011-0294	2010/08/02	▽=0	4 PLACES ± ---	± ---	EIK	1988/03/10	4:1	INCH	⊙	4 SIDES SHROUDED HEADER	SDA-70567-****	2 OF 5
DRWN:MS BARRA	1988/03/10	▽=0	3 PLACES ± ---	± .005	EIK	1988/03/10				HIGH TEMP, (2.54)/.100		
CHKD:DMORGAN	2010/08/03	▽=0	2 PLACES ± 0.13	± .010	EIK	1988/03/10				GRID W/ (0.64)/.025 PINS		
APPR:MBANAKIS		▽=0	1 PLACE ± 0.25	± ---		2010/03/31				MOLEX INCORPORATED		
			ANGULAR ± 1/2°		APPROVED BY							
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SMILLER							
					SEE TABLE							
					THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1
ENGINEERING NUMBER A-70567	MANUFACTURE RELEASE STATUS					E REF.	C ±.015 (0.38)				CONNECTOR END PLATING		P.C. BOARD END PLATING		PACKAGING INFORMATION PK-70873--				
											TYPE	D MEAS.	TYPE	F MEAS.					
-0001/-0034	R.F.M.					.130 (3.30)	.315 (8.00)				TIN	.100 (2.54)	TIN	.050 (1.27)	0018				
-0035/-0068	R.F.M.					.200 (5.08)	.315 (8.00)				TIN	.100 (2.54)	TIN	.050 (1.27)	0018				
-0069/-0102	R.F.M.					.130 (3.30)	.315 (8.00)				15 GOLD	.100 (2.54)	TIN	.050 (1.27)	0018				
-0103/-0136	R.F.M.					.200 (5.08)	.315 (8.00)				15 GOLD	.100 (2.54)	TIN	.050 (1.27)	0018				
-0137/-0170	R.F.M.					.130 (3.30)	.315 (8.00)				30 GOLD	.100 (2.54)	TIN	.050 (1.27)	0018				
-0171/-0204	R.F.M.					.200 (5.08)	.315 (8.00)				30 GOLD	.100 (2.54)	TIN	.050 (1.27)	0018				

NO. OF CKTS	OPTION "A"			OPTION "A"			OPTION "A"			OPTION "A"			OPTION "A"			OPTION "A"						NO. OF CKTS
	EDP NUMBER	ENG NUMBER		EDP NUMBER	ENG NUMBER		EDP NUMBER	ENG NUMBER		EDP NUMBER	ENG NUMBER		EDP NUMBER	ENG NUMBER		EDP NUMBER	ENG NUMBER		EDP NUMBER	ENG NUMBER		
06	15-80-0061	A-70567-0001		70567-0035	A-70567-0035		15-80-0063	A-70567-0069		70567-0103	A-70567-0103		15-80-0065	A-70567-0137		70567-0171	A-70567-0171					06
08	15-80-0081	A-70567-0002		70567-0036	A-70567-0036		15-80-0083	A-70567-0070		70567-0104	A-70567-0104		15-80-0085	A-70567-0138		70567-0172	A-70567-0172					08
10	15-80-0101	A-70567-0003		70567-0037	A-70567-0037		15-80-0103	A-70567-0071		70567-0105	A-70567-0105		15-80-0105	A-70567-0139		70567-0173	A-70567-0173					10
12	15-80-0121	A-70567-0004		70567-0038	A-70567-0038		15-80-0123	A-70567-0072		70567-0106	A-70567-0106		15-80-0125	A-70567-0140		70567-0174	A-70567-0174					12
14	15-80-0141	A-70567-0005		70567-0039	A-70567-0039		15-80-0143	A-70567-0073		70567-0107	A-70567-0107		15-80-0145	A-70567-0141		70567-0175	A-70567-0175					14
16	15-80-0161	A-70567-0006		70567-0040	A-70567-0040		15-80-0163	A-70567-0074		70567-0108	A-70567-0108		15-80-0165	A-70567-0142		70567-0176	A-70567-0176					16
18	15-80-0181	A-70567-0007		70567-0041	A-70567-0041		15-80-0183	A-70567-0075		70567-0109	A-70567-0109		15-80-0185	A-70567-0143		70567-0177	A-70567-0177					18
20	15-80-0201	A-70567-0008		70567-0042	A-70567-0042		15-80-0203	A-70567-0076		70567-0110	A-70567-0110		15-80-0205	A-70567-0144		70567-0178	A-70567-0178					20
22	15-80-0221	A-70567-0009		70567-0043	A-70567-0043		15-80-0223	A-70567-0077		70567-0111	A-70567-0111		15-80-0225	A-70567-0145		70567-0179	A-70567-0179					22
24	15-80-0241	A-70567-0010		70567-0044	A-70567-0044		15-80-0243	A-70567-0078		70567-0112	A-70567-0112		15-80-0245	A-70567-0146		70567-0180	A-70567-0180					24
26	15-80-0261	A-70567-0011		70567-0045	A-70567-0045		15-80-0263	A-70567-0079		70567-0113	A-70567-0113		15-80-0265	A-70567-0147		70567-0181	A-70567-0181					26
28	15-80-0281	A-70567-0012		70567-0046	A-70567-0046		15-80-0283	A-70567-0080		70567-0114	A-70567-0114		15-80-0285	A-70567-0148		70567-0182	A-70567-0182					28
30	15-80-0301	A-70567-0013		70567-0047	A-70567-0047		15-80-0303	A-70567-0081		70567-0115	A-70567-0115		15-80-0305	A-70567-0149		70567-0183	A-70567-0183					30
32	15-80-0321	A-70567-0014		70567-0048	A-70567-0048		15-80-0323	A-70567-0082		70567-0116	A-70567-0116		15-80-0325	A-70567-0150		70567-0184	A-70567-0184					32
34	15-80-0341	A-70567-0015		70567-0049	A-70567-0049		15-80-0343	A-70567-0083		70567-0117	A-70567-0117		15-80-0345	A-70567-0151		70567-0185	A-70567-0185					34
36	15-80-0361	A-70567-0016		70567-0050	A-70567-0050		15-80-0363	A-70567-0084		70567-0118	A-70567-0118		15-80-0365	A-70567-0152		70567-0186	A-70567-0186					36
38	15-80-0381	A-70567-0017		70567-0051	A-70567-0051		15-80-0383	A-70567-0085		70567-0119	A-70567-0119		15-80-0385	A-70567-0153		70567-0187	A-70567-0187					38
40	15-80-0401	A-70567-0018		70567-0052	A-70567-0052		15-80-0403	A-70567-0086		70567-0120	A-70567-0120		15-80-0405	A-70567-0154		70567-0188	A-70567-0188					40
42	15-80-0421	A-70567-0019		70567-0053	A-70567-0053		15-80-0423	A-70567-0087		70567-0121	A-70567-0121		15-80-0425	A-70567-0155		70567-0189	A-70567-0189					42
44	15-80-0441	A-70567-0020		70567-0054	A-70567-0054		15-80-0443	A-70567-0088		70567-0122	A-70567-0122		15-80-0445	A-70567-0156		70567-0190	A-70567-0190					44
46	15-80-0461	A-70567-0021		70567-0055	A-70567-0055		15-80-0463	A-70567-0089		70567-0123	A-70567-0123		15-80-0465	A-70567-0157		70567-0191	A-70567-0191					46
48	15-80-0481	A-70567-0022		70567-0056	A-70567-0056		15-80-0483	A-70567-0090		70567-0124	A-70567-0124		15-80-0485	A-70567-0158		70567-0192	A-70567-0192					48
50	15-80-0501	A-70567-0023		70567-0057	A-70567-0057		15-80-0503	A-70567-0091		70567-0125	A-70567-0125		15-80-0505	A-70567-0159		70567-0193	A-70567-0193					50
52	15-80-0521	A-70567-0024		70567-0058	A-70567-0058		15-80-0523	A-70567-0092		70567-0126	A-70567-0126		15-80-0525	A-70567-0160		70567-0194	A-70567-0194					52
54	15-80-0541	A-70567-0025		70567-0059	A-70567-0059		15-80-0543	A-70567-0093		70567-0127	A-70567-0127		15-80-0545	A-70567-0161		70567-0195	A-70567-0195					54
56	15-80-0561	A-70567-0026		70567-0060	A-70567-0060		15-80-0563	A-70567-0094		70567-0128	A-70567-0128		15-80-0565	A-70567-0162		70567-0196	A-70567-0196					56
58	15-80-0581	A-70567-0027		70567-0061	A-70567-0061		15-80-0583	A-70567-0095		70567-0129	A-70567-0129		15-80-0585	A-70567-0163		70567-0197	A-70567-0197					58
60	15-80-0601	A-70567-0028		70567-0062	A-70567-0062		15-80-0603	A-70567-0096		70567-0130	A-70567-0130		15-80-0605	A-70567-0164		70567-0198	A-70567-0198					60
62	15-80-0621	A-70567-0029		70567-0063	A-70567-0063		15-80-0623	A-70567-0097		70567-0131	A-70567-0131		15-80-0625	A-70567-0165		70567-0199	A-70567-0199					62
64	15-80-0641	A-70567-0030		70567-0064	A-70567-0064		15-80-0643	A-70567-0098		70567-0132	A-70567-0132		15-80-0645	A-70567-0166		70567-0200	A-70567-0200					64
66	15-80-0661	A-70567-0031		70567-0065	A-70567-0065		15-80-0663	A-70567-0099		70567-0133	A-70567-0133		15-80-0665	A-70567-0167		70567-0201	A-70567-0201					66
68	15-80-0681	A-70567-0032		70567-0066	A-70567-0066		15-80-0683	A-70567-0100		70567-0134	A-70567-0134		15-80-0685	A-70567-0168		70567-0202	A-70567-0202					68
70	15-80-0701	A-70567-0033		70567-0067	A-70567-0067		15-80-0703	A-70567-0101		70567-0135	A-70567-0135		15-80-0705	A-70567-0169		70567-0203	A-70567-0203					70
72	15-80-0721	A-70567-0034		70567-0068	A-70567-0068		15-80-0723	A-70567-0102		70567-0136	A-70567-0136		15-80-0725	A-70567-0170		70567-0204	A-70567-0204					72

SEE SHEETS 1 & 2

EC NO: UCP2011-0294

J

DRWN:MS BARBA

CHKD:JORGAN

APPR:HEAVAKUS

2010/08/02

1988/03/10

2010/08/03

REV

QUALITY SYMBOLS
▽=0
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)
mm INCH
4 PLACES ± --- ± ---
3 PLACES ± --- ± .005
2 PLACES ± 0.13 ± .010
1 PLACE ± 0.25 ± ---
ANGULAR ±1/2°
DRAFT WHERE APPLICABLE
MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN
DRAWN BY DATE
EIK 1988/03/10
CHECKED BY DATE
EIK 1988/03/10
APPROVED BY DATE
SMILLER 2010/03/31
MATERIAL NO.
SIZE D

SCALE
1:1
DESIGN UNITS
INCH
THIRD ANGLE PROJECTION
4 SIDES SHROUDED HEADER
HIGH TEMP. (2.54)/.100
GRID W/ (.064)/.025 PINS
MOLEX INCORPORATED
DOCUMENT NO.
SDA-70567-****
SHEET NO.
3 OF 5

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1				
M	ENGINEERING NUMBER A-70567	MANUFACTURE RELEASE STATUS					E REF.	C ±.015 (0.38)				CONNECTOR END PLATING		P.C. BOARD END PLATING		PACKAGING INFORMATION PK-70873-								
												TYPE		D MEAS.	TYPE									F MEAS.
L	-0205/-0238	R.F.M.					.130 (3.30)	.315 (8.00)				TIN		.100 (2.54)	TIN		.050 (1.27)	0018						
	-0239/-0272	R.F.M.					.200 (5.08)	.315 (8.00)				TIN		.100 (2.54)	TIN		.050 (1.27)	0018						
	-0273/-0306	R.F.M.					.130 (3.30)	.315 (8.00)				15 GOLD		.100 (2.54)	TIN		.050 (1.27)	0018						
	-0307/-0340	R.F.M.					.200 (5.08)	.315 (8.00)				15 GOLD		.100 (2.54)	TIN		.050 (1.27)	0018						
K	-0341/-0374	R.F.M.					.130 (3.30)	.315 (8.00)				30 GOLD		.100 (2.54)	TIN		.050 (1.27)	0018						
	-0375/-0408	R.F.M.					.200 (5.08)	.315 (8.00)				30 GOLD		.100 (2.54)	TIN		.050 (1.27)	0018						
J																								

NO. OF CKTS	OPTION "B"		OPTION "B"		OPTION "B"		OPTION "B"		OPTION "B"		OPTION "B"		OPTION "B"								NO. OF CKTS
	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	
06	IS-80-0067	A-70567-0205	70567-0239	A-70567-0239	IS-80-0069	A-70567-0273	70567-0307	A-70567-0307	IS-80-1061	A-70567-0341	70567-0375	A-70567-0375									06
08	IS-80-0087	A-70567-0206	70567-0240	A-70567-0240	IS-80-0089	A-70567-0274	70567-0308	A-70567-0308	IS-80-1081	A-70567-0342	70567-0376	A-70567-0376									08
10	IS-80-0107	A-70567-0207	70567-0241	A-70567-0241	IS-80-0109	A-70567-0275	70567-0309	A-70567-0309	IS-80-1101	A-70567-0343	70567-0377	A-70567-0377									10
12	IS-80-0127	A-70567-0208	70567-0242	A-70567-0242	IS-80-0129	A-70567-0276	70567-0310	A-70567-0310	IS-80-1121	A-70567-0344	70567-0378	A-70567-0378									12
14	IS-80-0147	A-70567-0209	70567-0243	A-70567-0243	IS-80-0149	A-70567-0277	70567-0311	A-70567-0311	IS-80-1141	A-70567-0345	70567-0379	A-70567-0379									14
16	IS-80-0167	A-70567-0210	70567-0244	A-70567-0244	IS-80-0169	A-70567-0278	70567-0312	A-70567-0312	IS-80-1161	A-70567-0346	70567-0380	A-70567-0380									16
18	IS-80-0187	A-70567-0211	70567-0245	A-70567-0245	IS-80-0189	A-70567-0279	70567-0313	A-70567-0313	IS-80-1181	A-70567-0347	70567-0381	A-70567-0381									18
20	IS-80-0207	A-70567-0212	70567-0246	A-70567-0246	IS-80-0209	A-70567-0280	70567-0314	A-70567-0314	IS-80-1201	A-70567-0348	70567-0382	A-70567-0382									20
22	IS-80-0227	A-70567-0213	70567-0247	A-70567-0247	IS-80-0229	A-70567-0281	70567-0315	A-70567-0315	IS-80-1221	A-70567-0349	70567-0383	A-70567-0383									22
24	IS-80-0247	A-70567-0214	70567-0248	A-70567-0248	IS-80-0249	A-70567-0282	70567-0316	A-70567-0316	IS-80-1241	A-70567-0350	70567-0384	A-70567-0384									24
26	IS-80-0267	A-70567-0215	70567-0249	A-70567-0249	IS-80-0269	A-70567-0283	70567-0317	A-70567-0317	IS-80-1261	A-70567-0351	70567-0385	A-70567-0385									26
28	IS-80-0287	A-70567-0216	70567-0250	A-70567-0250	IS-80-0289	A-70567-0284	70567-0318	A-70567-0318	IS-80-1281	A-70567-0352	70567-0386	A-70567-0386									28
30	IS-80-0307	A-70567-0217	70567-0251	A-70567-0251	IS-80-0309	A-70567-0285	70567-0319	A-70567-0319	IS-80-1301	A-70567-0353	70567-0387	A-70567-0387									30
32	IS-80-0327	A-70567-0218	70567-0252	A-70567-0252	IS-80-0329	A-70567-0286	70567-0320	A-70567-0320	IS-80-1321	A-70567-0354	70567-0388	A-70567-0388									32
34	IS-80-0347	A-70567-0219	70567-0253	A-70567-0253	IS-80-0349	A-70567-0287	70567-0321	A-70567-0321	IS-80-1341	A-70567-0355	70567-0389	A-70567-0389									34
36	IS-80-0367	A-70567-0220	70567-0254	A-70567-0254	IS-80-0369	A-70567-0288	70567-0322	A-70567-0322	IS-80-1361	A-70567-0356	70567-0390	A-70567-0390									36
38	IS-80-0387	A-70567-0221	70567-0255	A-70567-0255	IS-80-0389	A-70567-0289	70567-0323	A-70567-0323	IS-80-1381	A-70567-0357	70567-0391	A-70567-0391									38
40	IS-80-0407	A-70567-0222	70567-0256	A-70567-0256	IS-80-0409	A-70567-0290	70567-0324	A-70567-0324	IS-80-1401	A-70567-0358	70567-0392	A-70567-0392									40
42	IS-80-0427	A-70567-0223	70567-0257	A-70567-0257	IS-80-0429	A-70567-0291	70567-0325	A-70567-0325	IS-80-1421	A-70567-0359	70567-0393	A-70567-0393									42
44	IS-80-0447	A-70567-0224	70567-0258	A-70567-0258	IS-80-0449	A-70567-0292	70567-0326	A-70567-0326	IS-80-1441	A-70567-0360	70567-0394	A-70567-0394									44
46	IS-80-0467	A-70567-0225	70567-0259	A-70567-0259	IS-80-0469	A-70567-0293	70567-0327	A-70567-0327	IS-80-1461	A-70567-0361	70567-0395	A-70567-0395									46
48	IS-80-0487	A-70567-0226	70567-0260	A-70567-0260	IS-80-0489	A-70567-0294	70567-0328	A-70567-0328	IS-80-1481	A-70567-0362	70567-0396	A-70567-0396									48
50	IS-80-0507	A-70567-0227	70567-0261	A-70567-0261	IS-80-0509	A-70567-0295	70567-0329	A-70567-0329	IS-80-1501	A-70567-0363	70567-0397	A-70567-0397									50
52	IS-80-0527	A-70567-0228	70567-0262	A-70567-0262	IS-80-0529	A-70567-0296	70567-0330	A-70567-0330	IS-80-1521	A-70567-0364	70567-0398	A-70567-0398									52
54	IS-80-0547	A-70567-0229	70567-0263	A-70567-0263	IS-80-0549	A-70567-0297	70567-0331	A-70567-0331	IS-80-1541	A-70567-0365	70567-0399	A-70567-0399									54
56	IS-80-0567	A-70567-0230	70567-0264	A-70567-0264	IS-80-0569	A-70567-0298	70567-0332	A-70567-0332	IS-80-1561	A-70567-0366	70567-0400	A-70567-0400									56
58	IS-80-0587	A-70567-0231	70567-0265	A-70567-0265	IS-80-0589	A-70567-0299	70567-0333	A-70567-0333	IS-80-1581	A-70567-0367	70567-0401	A-70567-0401									58
60	IS-80-0607	A-70567-0232	70567-0266	A-70567-0266	IS-80-0609	A-70567-0300	70567-0334	A-70567-0334	IS-80-1601	A-70567-0368	70567-0402	A-70567-0402									60
62	IS-80-0627	A-70567-0233	70567-0267	A-70567-0267	IS-80-0629	A-70567-0301	70567-0335	A-70567-0335	IS-80-1621	A-70567-0369	70567-0403	A-70567-0403									62
64	IS-80-0647	A-70567-0234	70567-0268	A-70567-0268	IS-80-0649	A-70567-0302	70567-0336	A-70567-0336	IS-80-1641	A-70567-0370	70567-0404	A-70567-0404									64
66	IS-80-0667	A-70567-0235	70567-0269	A-70567-0269	IS-80-0669	A-70567-0303	70567-0337	A-70567-0337	IS-80-1661	A-70567-0371	70567-0405	A-70567-0405									66
68	IS-80-0687	A-70567-0236	70567-0270	A-70567-0270	IS-80-0689	A-70567-0304	70567-0338	A-70567-0338	IS-80-1681	A-70567-0372	70567-0406	A-70567-0406									68
70	IS-80-0707	A-70567-0237	70567-0271	A-70567-0271	IS-80-0709	A-70567-0305	70567-0339	A-70567-0339	IS-80-1701	A-70567-0373	70567-0407	A-70567-0407									70
72	IS-80-0727	A-70567-0238	70567-0272	A-70567-0272	IS-80-0729	A-70567-0306	70567-0340	A-70567-0340	IS-80-1721	A-70567-0374	70567-0408	A-70567-0408									72

SEE SHEETS 1 & 2 EC NO: UCP 2011-0294 DRAWN BY: BARRA CHKD BY: MORAN APPROV BY: S REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 1:1		DESIGN UNITS INCH		THIRD ANGLE PROJECTION				
		mm INCH		DRAWN BY DATE		CHECKED BY DATE		TITLE		4 SIDES SHROUDED HEADER HIGH TEMP. (2.54)/100 GRID W/ (0.64)/025 PINS				
		4 PLACES ± --- ± --- 3 PLACES ± --- ± .005 2 PLACES ± 0.13 ± .010 1 PLACE ± 0.25 ± --- ANGULAR ±1/2°		EIK 1988/03/10 EIK 1988/03/10		APPROVED BY DATE		MATERIAL NO.						
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SMILLER 2010/03/31		MOLEX INCORPORATED						
				DOCUMENT NO.		SDA-70567-****		SHEET NO.		4 OF 5				
				SIZE D		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

