


Lamp Specification

Wamco Part No.	Envelope Size	Base Type	Rating	Filament Shape
WL-356	G3-1/2	BA9s	28V .17A	C-2F

Test Volts	Current (A)			Light Output (MSCP)			Life Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
28	.153	.170	.187	2.62	3.50	4.38	500 Hrs

Dimensional Characteristics:

1. L.C.L. = .50" (12.7mm)
2. Base = Nickel-plated Brass Construction.



Title:

**G3-1/2 Miniature Bayonet Base Lamp
28V .170A Vacuum**

Drawn	6/3/02	CI	Notes: Unless otherwise specified, all dimensions are in inches.
Checked	6/4/02	EB	
Approved	6/4/02	EB	